


Specification Sheet

Part Number: TYHCA-Z



Handi-Card Wire and Cable Markers, .25" x 1.5", Sequence Letter A-Z, 36/Card, TYHC, White, 25/pkg

Article Number

598-00190

Type

TYHCA-Z

Color

White (WH)

Features & Benefits

- Handi-Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing.
- Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card.
- Markers are pre-printed so no additional post printing is required, saving time and money.
- Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.

Quantity Per

pack

Product Description

HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.

Short Description

Handi-Card Wire and Cable Markers, .25" x 1.5", Sequence Letter A-Z, 36/Card, TYHC, White, 25/pkg

Global Part Name

TYHCA-Z-TYHC-WH

Technical Description

Handi-Card, .25" X 1.5", Sequence Letter A-Z, 36 Per Card, White

Length L (Imperial)

1.5

Length L (Metric)

38.1

Width W (Imperial)

0.25

Width W (Metric)

6.35

Bundle Diameter Min (Imperial)

.13

Bundle Diameter Min (Metric)

3.40

Bundle Diameter Max (Imperial)

0.29

Bundle Diameter Max (Metric)

7.50

Height H (Imperial)

1.5

Height H (Metric)

38.1

Outside Diameter Max(Imperial)

0.29

Outside Diameter Min (metric) 3.40

Outside Diameter Min(Imperial) 0.13

Outside Diameter Max (metric) 7.50

Material Vinyl Cloth (TYHC)

Material Shortcut TYHC

Adhesive Rubber

Halogen free No

Adhesive Operating Temperature -40°F to +248°F (-40°C to +120°C)

Operating Temperature (Metric) -40°F to +248°F (-40°C to +120°C)

Reach Complaint(Article 33) No

ROHS Complaint Yes

Package Quantity(Imperial) 25

Package Quantity (Metric) 25

Customs Number 5903103000

Labels per Column 1

