

## Specification Sheet

Part Number: GSTJ6AU-GY



**Article Number**

852-25108

**Type**

GSTJ6AU-GY

**Color**

Gray (GY)

**Features & Benefits**

- The slim-line design of the jack allows for a maximum of 24 modules to be fitted into a standard 19" panel.
- Single termination design provides consistent, repeatable terminations.
- The wiring manifold incorporates both TIA 568A and B wiring schemes as well as strain relief for the cable.
- Configured to both TIA 568A and 568B wiring schemes for installation versatility.
- Suitable for air handling spaces, ideal for installation of WAPs and IP devices.

**Quantity Per**

bag

**Product Description**

The HellermannTyton GST keystone jack provides a common termination method across Category 6A performance standards. The Category 6A patented contact design uses innovative alien crosstalk cancellation technology, ensuring industry leading performance. The slim-line design's reduced depth means there is more space at the rear of the module which allows for the higher bend radius required for large diameter cables and that they can be used in installation where shallow trunking is being used.

**Short Description**

GST Category 6A UTP Modular Keystone Jack, Plenum Rated, Gray, 1/bag

**Global Part Name**

GSTJ6AU-GY

**Technical Description**

The design of the GST Category 6A Keystone Jack has an integrated wire manifold and lid which provides integral strain relief for the cable and which enables the use of the GST Termination Tool for quick and easy installation on site. The GST Category 6a Keystone Jacks are tested to exceed the latest published versions of ISO/IEC 11801, BS/EN50173 and ANSI/TIA/EIA 568-C Category 6A. The Alpha Label software package is available for download at [www.htdata.co.uk](http://www.htdata.co.uk) and enables straight forward port labeling. The GST Category 6A Keystone Jack offers backward compatibility with Category 6, Category 5e, Category 5 and voice products.

**Length L (Imperial)**

0.91

**Length L (Metric)**

16.5

**Width W (Imperial)**

0.65

**Width W (Metric)**

16.5

**Height H (Imperial)**

0.63

**Height H (Metric)**

23.3

**Depth D (imperial)**

1.54

**Depth D (metric)**

38.0

**UL Listed (US and Canada)**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

8536695050

**Weight (Metric)**

0.006