

## Specification Sheet

Part Number: GSTJC6U-BR



**Article Number**

852-25117

**Type**

GSTJC6U-BR

**Color**

Brown (BN)

### Features & Benefits

- The slim-line design of the jack allows for a maximum of 24 modules to be fitted into a standard 19" panel.
- Single termination design provides consistent, repeatable terminations.
- The wiring manifold incorporates both TIA 568A and B wiring schemes as well as strain relief for the cable.
- Exceeds Category 6 performance standards, providing the highest quality standards.
- Suitable for air handling spaces, ideal for installation of WAPs and IP devices.

**Quantity Per**

bag

### Product Description

The GST keystone jack provides a common termination method to exceed Category 6 performance standards. The slim-line design's reduced depth means there is more space at the rear of the module which allows for the higher bend radius required for large diameter cables and that they can be used in shallow trunking applications.

**Short Description**

GST Category 6 UTP Modular Keystone Jack, Plenum Rated, Brown, 1/bag

**Global Part Name**

GSTJC6U-BR

**Technical Description**

The design of the GST Keystone Jack has an integrated wire manifold and lid which provides integral strain relief for the cable and which enables the use of the GST Termination Tool for quick and easy installation on site.

**Length L (Imperial)**

0.91

**Length L (Metric)**

16.5

**Width W (Imperial)**

0.65

**Width W (Metric)**

16.5

**Height H (Imperial)**

0.63

**Height H (Metric)**

23.3

**Depth D (imperial)**

1.54

**Depth D (metric)**

38.0

**UL Listed (US and Canada)**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

8536695050

**Weight (Metric)**

0.006