

Specification Sheet

Part Number: GSTJC6U-WH

Product Image GST Category 6 UTP Modular Keystone Jack, Plenum Rated, White, 1/bag

Article Number	852-25125
Type	GSTJC6U-WH
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• The slim-line design of the jack allows for a maximum of 24 modules to be fitted into a standard 19" panel.• Single termination design provides consistent, repeatable terminations.• The wiring manifold incorporates both TIA 568A and B wiring schemes as well as strain relief for the cable.• Exceeds Category 6 performance standards, providing the highest quality standards.• Suitable for air handling spaces, ideal for installation of WAPs and IP devices.
Quantity Per	bag
Product Description	The GST keystone jack provides a common termination method to exceed Category 6 performance standards. The slim-line design's reduced depth means there is more space at the rear of the module which allows for the higher bend radius required for large diameter cables and that they can be used in shallow trunking applications.
Short Description	GST Category 6 UTP Modular Keystone Jack, Plenum Rated, White, 1/bag
Global Part Name	GSTJC6U-WH
Technical Description	The design of the GST Keystone Jack has an integrated wire manifold and lid which provides integral strain relief for the cable and which enables the use of the GST Termination Tool for quick and easy installation on site.

Length L (Imperial)

0.91

Length L (Metric)

16.5

Width W (Imperial)

0.65

Width W (Metric)

16.5

Height H (Imperial)

0.63

Height H (Metric)

23.3

Depth D (imperial)

1.54

Depth D (metric)

38.0

UL Listed (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

8536695050

Weight (Metric)

0.006

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)