

Specification Sheet

Part Number: P108-32-MOD



Modular Patch Panel 32 Port, 2U, Steel, Black, 1/box

Article Number	853-19204
Type	P108-32-MOD
Color	Black (BK)
Features & Benefits	• The modular design provides flexibility with the panel for customization of different applications including coax, voice, audio, video and fiber. • Once the connectors are snapped into the panel, they are flush with the front of the plate providing an aesthetic look.
Quantity Per	box
Product Description	The modular patch panel is designed to accept HellermannTyton Category 6A, 6 and 5e UTP modular jacks and connectors, providing flexibility in multimedia installations. These modular panels can be mounted to any standard EIA 19" rack, cabinet or wall mount patch panel bracket. HellermannTyton pre-numbered modular patch panels are available in 12,16, 24, 32 and 48 port configurations.

Short Description	Modular Patch Panel 32 Port, 2U, Steel, Black, 1/box
Global Part Name	P108-32-MOD
Technical Description	Modular Patch Panel 32 Port, 2U, Steel, Black
Length L (Imperial)	19.0
Length L (Metric)	482.6
Height H (Imperial)	3.50
Height H (Metric)	88.90
Material	Steel (ST)
Material Shortcut	ST
UL Listed (US and Canada)	Yes
UL Listed (US	Yes
Package Quantity(Imperial)	1
Package Quantity (Metric)	1
Customs Number	9030400000

