

## Specification Sheet

Part Number: PP24SMOD6ASRS



Category 6A 24 Port Sliding Shielded Patch Panel With Rack-Snaps, 1U, 1/box

**Article Number**

853-55001

**Type**

PP24G6A-PA1URS-SL.XX

**Color**

Black (BK)

**Features & Benefits**

- 24 shielded Deca<sup>10</sup>Category 6A/6 ports in 1U
- Dual labelling fields
- 360° shielding eliminates alien crosstalk
- Supplied with Cage Nuts
- Also available as a fixed panel

**Product Description**

The Modular FTP Sliding Patch Panel is designed to provide a complete shielded solution and accepts 24 shielded Deca<sup>10</sup> Category 6A/6 keystone jacks in 1U of space offering 24 RJ45 ports. The patch panel is fitted with an integral earthing plate and includes a rear cable management system. The shielded Category 6A/Category 6 products are designed to support any data or voice protocol that is capable of utilising a Category 6A/Category 6 cabling system.

**Short Description**

Category 6A 24 Port Sliding Shielded Patch Panel With Rack-Snaps, 1U, 1/box

<b>Global Part Name</b>	PP24G6A-PA1URS-SL.XX
<b>Technical Description</b>	Category 6A 24 Port Sliding Shielded Patch Panel With Rack-Snaps, 1U
<b>Port Count</b>	24
<b>Width W (Imperial)</b>	19.0
<b>Width W (Metric)</b>	483.0
<b>Height H (Imperial)</b>	1.7
<b>Height H (Metric)</b>	44.0
<b>Depth D (imperial)</b>	7.56
<b>Depth D (metric)</b>	192.0
<b>Package Quantity(Imperial)</b>	1
<b>Package Quantity (Metric)</b>	1
<b>Customs Number</b>	9030400000

