

Specification Sheet

Part Number: GT.50X110C2W



Article Number

854-44319

Type

GT.50X11W

Color

Black (BK)

Features & Benefits

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

Quantity Per

bag

Product Description

In situations where instant identification is needed, HellermannTyton provides Grip Ties with a white write-on area. This smudge-free surface is ideal for fast and easy identification with a ballpoint pen or felt-tip marker. The write-on area is approximately 3/8"H x 1-1/4"W. It is positioned in the center of the black 6", 8", and 11" straps, as well as spaced every 12" on the Grip Tie rolls.

Short Description

Grip Tie with White Write-On Area, 11.0" x .5", PA6/PP, Black, 100/pkg

Global Part Name

GT.50X11W

Minimum Tensile Strength (Imperial)

40.0

Minimum Tensile Strength (Metric)

177.93

Length L (Imperial)

11.0

Length L (Metric)

279.4

Width W (Imperial)

0.5

Width W (Metric)

12.7

Bundle Diameter Max (Imperial)

2.63

Bundle Diameter Max (Metric)

66.802

Material

Polyethylene (PE) Polyamide 6 (PA6)

Material Shortcut

PA66 PE

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)