

## Specification Sheet

Part Number: GT.50X110P2W



**Article Number**

854-44321

**Type**

GT.50X11W

**Color**

Black (BK)

**Features & Benefits**

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

**Quantity Per**

bag

**Product Description**

In situations where instant identification is needed, HellermannTyton provides Grip Ties with a white write-on area. This smudge-free surface is ideal for fast and easy identification with a ballpoint pen or felt-tip marker. The write-on area is approximately 3/8"H x 1-1/4"W. It is positioned in the center of the black 6", 8", and 11" straps, as well as spaced every 12" on the Grip Tie rolls.

**Short Description**

Grip Tie with White Write-On Area, 11.0" x .5", PA6/PP, Black, 10/pkg

Global Part Name

GT.50X11W

Minimum Tensile Strength (Imperial)

40.0

Minimum Tensile Strength (Metric)

177.93

Length L (Imperial)

11.0

Length L (Metric)

279.4

Width W (Imperial)

0.5

Width W (Metric)

12.7

Bundle Diameter Max (Imperial)

2.63

Bundle Diameter Max (Metric)

66.802

Material

Polyamide 6 (PA6) Polyethylene (PE)

Material Shortcut

PE PA66

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

3926909988

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)