

Specification Sheet

Part Number: GT.50X112P2



Article Number

854-44323

Type

GT.50X11

Color

Red (RD)

Features & Benefits

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

Quantity Per

bag

Product Description

The Grip Tie is a low-profile, one-piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Reusable, adjustable, releasable, and easy to install, it can be successfully opened and closed numerous times. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.

Short Description	Grip Tie Strap, 11.0" x .5", PA6/PP, Red, 10/pkg
Global Part Name	GT.50X11
Minimum Tensile Strength (Imperial)	40.0
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	11.0
Length L (Metric)	279.4
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Max (Imperial)	2.63
Bundle Diameter Max (Metric)	66.802
Material	Polyamide 6 (PA6) Polyethylene (PE)
Material Shortcut	PE PA66
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

3926909988