

Specification Sheet

Part Number: GT.50X12MP2V2



Article Number

854-44334

Type

GT.50X12

Color

Red Brown (RDBN)

Features & Benefits

- UL 94 V-2 flame rated material allows use in air handling spaces.
- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle diameters.

Quantity Per

bag

Product Description

HellermannTyton offers UL 94 V-2 flame rated Grip Ties for use in air handling spaces. Grip Ties are UL Listed in accordance with the National Electric Code regulations. Grip Ties are low-profile, one-piece fastening devices. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.

Short Description	Grip Tie, UL94V0-2 Flame Rated, .5" x 12.0", PA6/PP, Maroon, 10/pkg
Global Part Name	GT.50X12
Minimum Tensile Strength (Imperial)	40.0
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	12.0
Length L (Metric)	304.8
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Max (Imperial)	3.18
Bundle Diameter Max (Metric)	80.772
Material	Polyamide 6 (PA6) Polypropylene (PP)
Material Shortcut	PA6 PP
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

3926909988