

Specification Sheet

Part Number: GT.75X180MV2



Grip Tie Roll, UL94V0-2 Flame Rated, 180" Long, .75" Wide, PA6/PP, Maroon, 1/pkg

Article Number

854-44394

Type

GT.75X180

Color

Red Brown (RDBN)

Features & Benefits

- UL94V0-2 flame rate material allow use in air handling spaces.
- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

Quantity Per

bag

Product Description

For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

Short Description

Grip Tie Roll, UL94V0-2 Flame Rated, 180" Long, .75" Wide, PA6/PP, Maroon, 1/pkg

Global Part Name

GT.75X180

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

222.41

Length L (Imperial)

15.0

Length L (Metric)

4.5

Width W (Imperial)

0.75

Width W (Metric)

19.05

Material

Polypropylene (PP) Polyamide 6 (PA6)

Material Shortcut

PP PA6

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)