

Specification Sheet

Part Number: FERM18S



Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, Black, 1/pkg

Article Number

855-49200

Type

FERM18S

Color

Black (BK)

Features & Benefits

- Removable front and rear covers provide easy access to cables.
- Slide-out tray with easy-to-grip raised edge.
- Cable management spools for effective slack management.
- Optional splice trays to assist with cable splicing.
- Panel positioning for easier patch cords access.
- Round edge plastic fiber saddles for easier patch-cord routing.
- Meet ANSI/TIA/EIA 568-C standards.

Quantity Per

EA

Product Description

HellermannTyton's rack mount fiber enclosures are the ideal direct termination and splice solution of LAN applications capable of supporting up to 72 fibers. While offering easy-to-use front slide-out trays for effortless access to connections, enclosures are equipped with cable management and cable routing accessories to limit bend radius and add strain relief control. HellermannTyton's Rack Mount Fiber Enclosures easily fit into 19" or 23" racks.

Short Description

Rack Mount Fiber Enclosure-Unloaded, Accepts 3 LGX Adapter Panels, 1U, Black, 1/pkg

Global Part Name

FERM18S

Technical Description

Rack Mount Fiber Enclosure-Unloaded, Accepts 3 Adapter Panels for Fiber Counts 18/24, 1U, BK

Port Count

48 24 12

Length L (Imperial)

12.14

Length L (Metric)

308.4

Variant

Rack mount

Width W (Imperial)

17.0

Width W (Metric)

431.8

Height H (Imperial)

1.75

Height H (Metric)

44.50

Depth D (imperial)

12.14

Depth D (metric)

308.36

Package Quantity(Imperial)	1
Package Quantity (Metric)	1
Customs Number	8538907080
Weight (Metric)	6.80
Weight (Imperial)	15.0