

## Specification Sheet

Part Number: FERM36S



Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 2U, Black, 1/pkg

Article Number	855-49201
Type	FERM36S
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>• Removable front and rear covers provide easy access to cables.</li><li>• Slide-out tray with easy-to-grip raised edge.</li><li>• Cable management spools for effective slack management.</li><li>• Optional splice trays to assist with cable splicing.</li><li>• Panel positioning for easier patch cords access.</li><li>• Round edge plastic fiber saddles for easier patch-cord routing.</li><li>• Meet ANSI/TIA/EIA 568-C standards.</li></ul>
Quantity Per	box

**Product Description**

HellermannTyton's rack mount fiber enclosures are the ideal direct termination and splice solution of LAN applications capable of supporting up to 72 fibers. While offering easy-to-use front slide-out trays for effortless access to connections, enclosures are equipped with cable management and cable routing accessories to limit bend radius and add strain relief control. HellermannTyton's Rack Mount Fiber Enclosures easily fit into 19" or 23" racks.

**Short Description**

Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 2U, Black, 1/pkg

**Global Part Name**

FERM36S

**Technical Description**

Rack Mount Fiber Enclosure-Unloaded, Accepts 6 Adapter Panels for Fiber Counts 36/48, 2U, BK

**Port Count**

24 96 48

**Length L (Imperial)**

12.14

**Length L (Metric)**

308.4

**Variant**

Rack mount

**Width W (Imperial)**

17.0

**Width W (Metric)**

431.8

**Height H (Imperial)**

3.50

**Height H (Metric)**

88.90

**Depth D (imperial)**

12.14

**Depth D (metric)**

308.36

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

8538907080

**Weight (Imperial)**

17