

## Specification Sheet

Part Number: CL-R50-10



Cablelok R50 5.2 - 8.0 mm x 10, CR, Black, 1/pkg

**Article Number**

857-50154

**Type**

CABLELOK-R50-10

**Color**

Black (BK)

**Features & Benefits**

- Rapid installation requiring no specialized tools saves time and money.
- Highly repeatable – the quality of the seal is not dependent on the skill of the engineer.
- Tested beyond a 20-foot water head (58.8kPa), exhibiting excellent sealing properties.

**Quantity Per**

bag

**Product Description**

HellermannTyton's patented Cablelok mechanical seal enables fast, safe cable installation, providing a repeatable and consistent seal between the cable and the closure port with excellent non-leak performance. Installation times are typically reduced by up to 90 percent.

**Short Description**

Cablelok R50 5.2 - 8.0 mm x 10, CR, Black, 1/pkg

**Global Part Name**

CABLELOK-R50-10

**Technical Description**

The R Port Cablelok is a mechanical seal manufactured from external grade flexible polychloroprene. There are 11 Cablelok's which cover a cable range of 1.7mm – 9.5mm including three multi-hole versions to allow two cable drops from the same port and a port plug for blocking unused R sized drop ports.

**Port Count**

1

**Variant**

Round - R

**Material**

Chloroprene Rubber (CR)

**Material Shortcut**

CR

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

10

**Package Quantity (Metric)**

10

**Customs Number**

9030400000

**Content Unit(BMEcat)**

pcs.

