

Specification Sheet

Part Number: CL-R70-10



Cablelok R70 6.0 - 8.5 mm x 10, CR, Black, 1/pkg

Article Number	857-50168
Type	CABLELOK-R70-10
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Rapid installation requiring no specialized tools saves time and money.• Highly repeatable – the quality of the seal is not dependent on the skill of the engineer.• Tested beyond a 20-foot water head (58.8kPa), exhibiting excellent sealing properties.
Quantity Per	bag
Product Description	HellermannTyton's patented Cablelok mechanical seal enables fast, safe cable installation, providing a repeatable and consistent seal between the cable and the closure port with excellent non-leak performance. Installation times are typically reduced by up to 90 percent.
Short Description	Cablelok R70 6.0 - 8.5 mm x 10, CR, Black, 1/pkg

Global Part Name

CABLELOK-R70-10

Technical Description

The R Port Cablelok is a mechanical seal manufactured from external grade flexible polychloroprene. There are 11 Cablelok's which cover a cable range of 1.7mm – 9.5mm including three multi-hole versions to allow two cable drops from the same port and a port plug for blocking unused R sized drop ports.

Port Count

1

Variant

Round - R

Material

Chloroprene Rubber (CR)

Material Shortcut

CR

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

9030400000

Content Unit(BMEcat)

pcs.