

Specification Sheet

Part Number: CL-S50-10



Cablelok S50 16.0- 20.0 mm x 10, CR, Black, 1/pkg

Article Number

857-50174

Type

CABLELOK-S50-10

Color

Black (BK)

Features & Benefits

- Rapid installation requiring no specialized tools saves time and money.
- Highly repeatable – the quality of the seal is not dependent on the skill of the engineer.
- Tested beyond a 20-foot water head (58.8kPa), exhibiting excellent sealing properties.

Quantity Per

bag

Product Description

HellermannTyton's patented Cablelok mechanical seal enables fast, safe cable installation, providing a repeatable and consistent seal between the cable and the closure port with excellent non-leak performance. Installation times are typically reduced by up to 90 percent.

Short Description

Cablelok S50 16.0- 20.0 mm x 10, CR, Black, 1/pkg

Global Part Name

CABLELOK-S50-10

Technical Description

The S Port Cablelok is a mechanical seal manufactured from external grade flexible polychloroprene. There are 6 Cablelok's which cover a cable range of 5.0mm – 20.0mm including one multi-hole version to allow two cable drops from the same port and a port plug for blocking unused S sized drop ports.

Port Count

1

Variant

Round - S

Material

Chloroprene Rubber (CR)

Material Shortcut

CR

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

9030400000

Content Unit(BMEcat)

pcs.