

Specification Sheet

Part Number: RNGPP1UHD-HHSS



Hybrid Modular Panel for High Density Copper (2) and Fiber Cassette (2), 1U, Steel, Black, 1/ctn

Article Number

859-30055

Type

RNGPPIUHD-HHSS

Color

Black (BK)

Product Description

The 1U RapidNet Hybrid Panel provides a simple 'Mix and Match' approach for both copper and fibre RapidNet. The panel offers capacity for the equivalent of 1U of fibre and 1U of copper in 1U of rack space, giving a saving of 1U of space each time the panel is used. The panels allow for a combination of 12 port high density copper RapidNet and 12 or 24 core fibre (direct terminated or MTP) or high density copper and RapidNet MTP VHD for up to 288 fibres. There are two configurations available.

Short Description

Hybrid Modular Panel for High Density Copper (2) and Fiber Cassette (2), 1U, Steel, Black, 1/ctn

Global Part Name

RNGPPIUHD-HHSS

Technical Description

Hybrid Modular Panel for High Density Copper (2) and Fiber Cassette (2), 1U, Steel, Black

Variant

Accessory

Width W (Imperial)

19.0

Width W (Metric)

483.0

Height H (Imperial)

1.7

Height H (Metric)

44.0

Depth D (imperial)

2.8

Depth D (metric)

72.0

Material

Steel (ST)

Material Shortcut

ST

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

9030400000

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)