

Specification Sheet

Part Number: ETST6610



Electrical Tape, .75" x 66' Roll, 7.0 mil Thick, PVC, White, 10 rolls/pkg

Article Number

904-00012

Type

ETST66

Color

White (WH)

Features & Benefits

- Heavy duty PVC tape is ideal for cold weather installations and is "weather resistant" for outdoor applications.
- Meets Mil-Std. MIL-1-24391-A.

Quantity Per

reel

Product Description

PVC electrical tape provides fast and easy color coding, cable splicing, terminating, and wire insulating. These conformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

Short Description

Electrical Tape, .75" x 66' Roll, 7.0 mil Thick, PVC, White, 10 rolls/pkg

Global Part Name

ETST66-PVC-WH

Minimum Tensile Strength (Imperial)

15.4

Length L (Imperial)

66.0

Length L (Metric)

20.12

Width W (Imperial)

0.75

Width W (Metric)

19.05

Thickness T (Imperial)

7.0

Material

Flexible Polyvinyl Chloride (PVC)

Material Shortcut

PVC

US MIL SPEC

MIL-1-7798-A

Operating Temperature (Metric)

+20°F to 176°F (-7°C to +80°C)

UL Listed (US)

Yes

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

3919102020

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)