

Specification Sheet

Part Number: 904-00357



Convoluted Tubing, Slit, 1.5" Dia, PEUV, Black with Orange Stripe, 1000ft/carton

Article Number	904-00357
Type	CTPUV120
Color	Black with Orange Stripe (BKSTOG)
Features & Benefits	<ul style="list-style-type: none">• Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.• Tubing provides full coverage where spiral wrap or other coverings may not be suitable.• In harsh applications the tubing provides resistance to crushing, impact, and abrasion.• Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.
Quantity Per	carton

Product Description

HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description

Convoluted Tubing, Slit, 1.5" Dia, PEUV, Black with Orange Stripe, 1000ft/carton

Global Part Name

CTPUV120-PEUV-BK

Length L (Imperial)

1000.0

Length L (Metric)

304.8

Diameter D (imperial)

1.947

Diameter D (metric)

49.45

Outside Diameter OD(Imperial)

1.647

Outside Diameter OD(metric)

41.83

Nominal Diameter (Imperial)

1.5

Nominal Diameter (Metric)

38.1

Wall Thickness WT (Imperial)

0.006

Wall Thickness WT (Metric)

0.152

Material	Polyethylene, UV-resistant (PEUV)
Material Shortcut	PEUV
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +199°F (-40°C to +93°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	304.80
Customs Number	3926909988