

Specification Sheet

Part Number: VFAP6SMMQSCZ



Article Number

904-00374

Type

VFAP6SMMQSCZ

Color

Aqua (AE)

Features & Benefits

- High performance zirconia ceramic ferrules allow for frequent, repeated insertion.
- Standard LC, SC, ST, MTP and MTRJ connector options to suit specific applications.
- “Snap lock” fixtures for easy and secure mounting.
- Meet ANSI/TIA/EIA 568-C standards.
- Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.
- GSA compliant panels meet TAA requirements for use in government projects.

Quantity Per

box

Product Description

For customized wall mount and rack mount fiber optic enclosures, HellermannTyton offers panel options featuring a variety of adapters to suit different preferences and applications. In addition to adapter panels with standard LC, SC, ST, MTP and MTRJ connections, HellermannTyton also offers custom solutions. Our adapter panels include options to accommodate OS1/2 in both standard and angled versions, as well as 62.5/125µm OM1, 50/125µm OM2 and 50/125µm 10 Gb OM3/4. HellermannTyton adapter panels are made with zirconia ceramic or phosphor bronze ferrules for minimal insertion loss contribution. Zirconia ceramic ferrules provided excellent durability and are an ideal choice for use in laser optimized multimode and single mode applications. HellermannTyton offers both standard and GSA compliant adapter panels. GSA compliant panels meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government projects.

Short Description

Fiber Adapter Panel Preloaded with 6 Simplex SC MM, Aqua, 1/pkg

Global Part Name

VFAP6SMMQSCZ-BU

Technical Description

FT Adapter Panel Preloaded with 6 Simplex SC MM, Aqua

Port Count

6

Length L (Imperial)

5.09

Length L (Metric)

129.3

Height H (Imperial)

1.14

Height H (Metric)

29.0

Material

Metal (MET)

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

8536700000