

## Specification Sheet

Part Number: FERM1UV



Rack Mount Fiber Enclosure-Unloaded, no door, Accepts 3 LGX Adapter Panels, 1U, Black, 1/pkg

**Article Number**

904-00689

**Type**

FERM1UV

**Color**

Black (BK)

**Features & Benefits**

- Removable front and rear covers provide easy access to cables.
- Slide-out tray with easy-to-grip raised edge.
- Cable management spools for effective slack management.
- Optional splice trays to assist with cable splicing.
- Panel positioning for easier patch cords access.
- Round edge plastic fiber saddles for easier patch-cord routing.
- Meet ANSI/TIA/EIA 568-C standards.

**Quantity Per**

box

**Product Description**

HellermannTyton rack mount enclosures are durable and support up to 1728 fibers. Rack enclosures work with standard 19" and 23" equipment racks and are designed to work with standard LGX adapter panels. HellermannTyton offers standard and GSA compliant rack mount enclosures. GSA compliant enclosures meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government projects.

**Short Description**

Rack Mount Fiber Enclosure-Unloaded, no door, Accepts 3 LGX Adapter Panels, 1U, Black, 1/pkg

**Global Part Name**

FERM1UV-MET-BK

**Technical Description**

Rack Mount Fiber Enclosure-Unloaded, no door, Accepts 3 Adapter Panels, 1U, BK

**Port Count**

72 18 36

**Length L (Imperial)**

8.15

**Length L (Metric)**

207.01

**Variant**

Rack mount

**Width W (Imperial)**

19.0

**Width W (Metric)**

482.6

**Height H (Imperial)**

1.75

**Height H (Metric)**

44.50

**Material**

Metal (MET)

**Material Shortcut**

MET

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

8538907080