

## Specification Sheet

Part Number: FESS2060



Fusion Splice Sleeve, Heat Shrink Style 2mm x 60mm (100 pack)

<b>Article Number</b>	904-00710
<b>Type</b>	FESS2060
<b>Color</b>	Silver (SR)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Splice sleeves to assist with cable splicing.</li></ul>
<b>Quantity Per</b>	box
<b>Product Description</b>	<p>For maximum organization, efficiency and utility, HellermannTyton offers splice sleeves and trays to assist in cable splicing applications. Fiber splice trays are available to accommodate 12 or 24 splices. Each tray provides space for mounting fiber splice protectors and excess fiber storage. Available in different shrink diameters, splice sleeves are constructed with a stainless steel inner tube and a polyolefin outer tube. Sleeves are heat bonded to ensure tubes maintain perfect alignment during shipping, handling and shrinking. Cable management spools organize cable slack.</p>
<b>Short Description</b>	Fusion Splice Sleeve, Heat Shrink Style 2mm x 60mm (100 pack)

**Global Part Name**

FESS2060-ML

**Technical Description**

Splice Sleeve, 2.0mm OD, 60mm long

**Port Count**

1

**Length L (Imperial)**

2.36

**Length L (Metric)**

60.0

**Variant**

Fusion splice sleeve

**Package Quantity(Imperial)**

100

**Package Quantity (Metric)**

100

**Customs Number**

9030400000