

Specification Sheet

Part Number: RNGFAP12DSMLC



RapidNet Fiber Adapter Panel 12 DUP, SM, LC Blue 1/pkg

Article Number

904-00772

Type

RNGFAP

Color

Blue (BU)

Features & Benefits

- Ideal for installations with limited access or restricted space.
- Available in in 6 or 12 hole configuration.
- Allows ruggedized fan-outs to be presented in RapidNet Panels.
- Fits into a standard RapidNet Panel.
- Supports a maximum of 1152 fibers in 1U of space.

Product Description

The RapidNet Fiber Adapter Panel is designed to allow the RapidNet solution to be used in areas with limited access or restricted space, where a RapidNet Cassette cannot be used. Panels are pre-loaded with adapters, which allow ruggedized fan-outs to be presented in RapidNet panels - offering a maximum of 288 fibers in a single adapter, or 1152 fibers in 1U of space.

Short Description

RapidNet Fiber Adapter Panel 12 DUP, SM, LC Blue 1/pkg

Global Part Name

RNGFAP-PL-BU

Technical Description

RapidNet Fiber Adapter Panel 12 DUP, SM, LC Blue

Port Count

24

Length L (Imperial)

2.1

Length L (Metric)

53.75

Variant

Modular Fiber Adapter Plate

Width W (Imperial)

4.0

Width W (Metric)

102.7

Height H (Imperial)

1.10

Height H (Metric)

27.80

Material

Plastic (PL)

Material Shortcut

PL

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

8536700000

Weight (Metric)

113.4

Weight (Imperial)

4