

## Specification Sheet

Part Number: RNGFAP6DMMSC



RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige 1/pkg

**Article Number**

904-00778

**Type**

RNGFAP

**Color**

Beige (BGE)

**Features & Benefits**

- Ideal for installations with limited access or restricted space.
- Available in in 6 or 12 hole configuration.
- Allows ruggedized fan-outs to be presented in RapidNet Panels.
- Fits into a standard RapidNet Panel.
- Supports a maximum of 1152 fibers in 1U of space.

**Product Description**

The RapidNet Fiber Adapter Panel is designed to allow the RapidNet solution to be used in areas with limited access or restricted space, where a RapidNet Cassette cannot be used. Panels are pre-loaded with adapters, which allow ruggedized fan-outs to be presented in RapidNet panels - offering a maximum of 288 fibers in a single adapter, or 1152 fibers in 1U of space.

**Short Description**

RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige 1/pkg

**Global Part Name**

RNGFAP-PL-BGE

**Technical Description**

RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige

**Port Count**

12

**Length L (Imperial)**

2.1

**Length L (Metric)**

53.75

**Variant**

Modular Fiber Adapter Plate

**Width W (Imperial)**

4.0

**Width W (Metric)**

102.7

**Height H (Imperial)**

1.10

**Height H (Metric)**

27.80

**Material**

Plastic (PL)

**Material Shortcut**

PL

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

8536700000

**Weight (Metric)**

113.4

**Weight (Imperial)**

4