

Specification Sheet

Part Number: VFA15SCSCOM2



FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg

Article Number

904-00819

Type

VFA15SCSCOM2

Color

Orange (OG)

Features & Benefits

- Pre-radiused zirconia ceramic ferrules for precision alignment.
- Industry standard LC, SC, ST or MTRJ connectors to suit specific applications.
- Available in 1-5 meter lengths.
- 3mm cordage.
- Color coded for easy identification.
- Individually quality tested for insertion and return loss.
- Meet ANSI/TIA/EIA 568-B standards.
- Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

Quantity Per

box

Product Description

For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and GSA compliant. Our standard jumpers combine quality with value, meeting all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, GSA compliant jumpers meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government contract projects.

Short Description

FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg

Global Part Name

VFA15SCSCOM2-GF-OG

Technical Description

FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange

Length L (Imperial)

49.2

Length L (Metric)

15.0

Material

Glass Fiber (GF)

Material Shortcut

GF

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

8544700000

Weight (Metric)

340.2

Weight (Imperial)

12.0