


Specification Sheet

Part Number: VFA15LCSCOM2



Article Number

904-00823

Type

VFA15LCSCOM2

Color

Orange (OG)

Features & Benefits

- Pre-radiused zirconia ceramic ferrules for precision alignment.
- Industry standard ST, SC, MTRJ or LC connectors to suit specific applications.
- Available in 1-5 meter lengths for a variety of applications.
- Color coded for easy identification.
- Individually quality tested for insertion and return loss.
- Meet ANSI/TIA/EIA 568-B standards.
- Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

Quantity Per

box

Product Description

For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high performance jumpers have additional features designed for high performance applications . Our high performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.

Short Description

FT LC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg

Global Part Name

VFA15LCSCOM2-GF-OG

Technical Description

FT LC - SC Duplex OM2 Fiber Assembly, 15M, Orange

Length L (Imperial)

49.2

Length L (Metric)

15.0

Material

Glass Fiber (GF)

Material Shortcut

GF

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

8544700000

Weight (Metric)

340.2

Weight (Imperial)

12.0