

Specification Sheet

Part Number: ORC4U



Out of Rack Connectivity, 4U, Steel, Black, 1/box

Article Number

904-00965

Type

ORC4U

Color

Black (BK)

Features & Benefits

- Maximizes cabling density outside of the cabinet/rack to reclaim data center floor space.
- Universal mounting brackets provide simple, flexible mounting options for ladder rack or overhead cable tray.
- Cable rings included for versatile cable routing and manageability for moves, adds or changes.
- CEA-310-E compliant mounting holes for compatibility with data center hardware.
- 12-gauge steel construction delivers 100-pound load rating.

Quantity Per

box

Product Description

HellermannTyton's Out of Rack connectivity solution provides 4U of space to accommodate patch panels or additional active hardware above cabinets and racks without consuming additional floor space. It can be used as a Zone Distribution Area or Equipment Distribution Area for increased scalability. Standard 19" rack mount accepts traditional copper and fiber panels as well as RapidNet® pre-terminated solutions for swift deployment. Included universal mounting brackets provide flexibility to mount the rack in multiple positions on common ladder rack and overhead cable tray systems. This allows for improved cable routing between pathways and cabinets or racks.

Short Description

Out of Rack Connectivity, 4U, Steel, Black, 1/box

Global Part Name

ORC4U-ST-BK

Width W (Imperial)

19.0

Width W (Metric)

482.6

Height H (Imperial)

8.39

Height H (Metric)

213.0

Depth D (imperial)

3.0

Depth D (metric)

76.2

Material

Steel (ST)

Material Shortcut

ST

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

9030400000