

TERMINALS

TOR (TAPE ON REEL) AVAILABLE

4 AWG RING TERMINALS



STUD SIZE	NON-INSULATED	VINYL	VINYL W/ SUPPORT SLEEVE	NYLON W/ SUPPORT SLEEVE	NYLON	HIGH TEMP 650°F	HIGH TEMP 900°F	HEAT SHRINK
10	4S5R1	-	-	-	FN4S5	-	-	-
1/4"	46R1	-	-	-	FN46	-	-	-
5/16"	48R1	-	-	-	FN48	-	-	-
3/8"	4S9R1	-	-	-	FN49	-	-	-
1/2"	413R1	-	-	-	FN413	-	-	-

2 AWG RING TERMINALS



STUD SIZE	NON-INSULATED	VINYL	VINYL W/ SUPPORT SLEEVE	NYLON W/ SUPPORT SLEEVE	NYLON	HIGH TEMP 650°F	HIGH TEMP 900°F	HEAT SHRINK
10	2S5R1	-	-	-	FN2S5	-	-	-
1/4"	2S6R1	-	-	-	FN2S6	-	-	-
5/16"	2S8R1	-	-	-	FN2S8	-	-	-
3/8"	29R1	-	-	-	FN29	-	-	-
7/16"	211R1	-	-	-	-	-	-	-
1/2"	213R1	-	-	-	FN213	-	-	-

LARGE NON-INSULATED RING TERMINALS



STUD SIZE	WIRE SIZE							
	1/0 AWG	2/0 AWG	3/0 AWG	4/0 AWG	250/300 MCM	300/350 MCM	400/500 MCM	500/600 MCM
1/4"	1/06R1	2/06R1	3/06R1	4/06R1	-	-	-	-
5/16"	1/08R1	2/08R1	3/08R1	4/08R1	1508R1	-	-	-
3/8"	1/09R1	2/09R1	3/09R1	4/09R1	1509R1	2009R1	2509R1	3009R1
7/16"	1/011R1	2/011R1	3/011R1	-	15011R1	-	-	-
1/2"	1/013R1	2/013R1	3/013R1	4/013R1	15013R1	20013R1	25013R1	30013R1
5/8"	1/016R1	2/016R1	3/016R1	4/016R1	15016R1	20016R1	25016R1	30016R1
3/4"	-	-	-	4/019R1	-	20019R1	-	-