

## NON-INSULATED FLAG TERMINALS



STUD SIZE	WIRE SIZE										
	22-16	16-14	12-10	8	6	4	2	1/0	2/0	3/0	4/0
8	AFG4	BFG4	-	-	-	-	-	-	-	-	-
10	AFG5	BFG5	DFG5	FG85	FG65/J	-	-	-	-	-	-
1/4"	-	BFG6	DFG6	FG86	FG66	FG46	FG26	FG1/06	-	-	-
5/16"	-	-	-	FG88	FG68	FG48	FG28	FG1/08	FG2/08	FG3/08	FG4/08
3/8"	-	-	-	FG89	FG69	FG49	FG29	FG1/09	FG2/09	FG3/09	FG4/09
1/2"	-	-	-	-	-	-	-	-	FG2/013	FG3/013	FG4/013
3/4"	-	-	-	4/019R1	-	-	-	-	-	-	-

## 26-22 AWG SPADE TERMINALS



STUD SIZE	NON-INSULATED	VINYL	VINYL W/ SUPPORT SLEEVE	NYLON W/ SUPPORT SLEEVE	NYLON	HIGH TEMP 650°F	HIGH TEMP 900°F	HEAT SHRINK
4	E3A	-	-	-	-	-	-	-
6	E3.7A	-	-	-	EFND3.7A/J	-	-	-
8	E4A	-	-	-	EFND4A/J	-	-	-

## 22-16 AWG SPADE TERMINALS



STUD SIZE	NON-INSULATED	VINYL	VINYL W/ SUPPORT SLEEVE	NYLON W/ SUPPORT SLEEVE	NYLON	HIGH TEMP 650°F	HIGH TEMP 900°F	HEAT SHRINK
4	AM3A	AFVLM3AR2	AFVDM3A	AFNDM3A	-	-	-	-
6	AS3A	AFVLS3AR2	AFVDS3A	AFNDS3A	-	-	-	AHS3A
8	AS4A	AFVLS4AR2	AFVDS4A	AFNDS4A	-	-	-	AHS4A
10	AM5A	AFVLM5AR2	AFVDM5A	AFNDM5A	-	-	-	AHS5A
1/4"	A6A	AFVL6AR2	AFVD6A	AFND6A	-	-	-	-

## 16-14 AWG SPADE TERMINALS



STUD SIZE	NON-INSULATED	VINYL	VINYL W/ SUPPORT SLEEVE	NYLON W/ SUPPORT SLEEVE	NYLON	HIGH TEMP 650°F	HIGH TEMP 900°F	HEAT SHRINK
8	B4A	BFVL4AR2	BFVD4A	BFND4A	-	-	-	BHS4A
10	B5A	BFVL5AR2	BFVD5A	BFND5A	-	-	-	BHS5A
1/4"	B6A	BFVL6AR2	BFVD6A	BFND6A	-	-	-	-