

Switches



Residential Grade Toggle and Decorator Switches



- Elongated strap with continuous plaster ears positions device flush to the wall surface
- Tough thermoplastic ultrasonically welded cover and base
- High-visibility yellow base for easy installation in low light working conditions
- Quiet snap action mechanism
- UL Listed and CSA Certified

Residential Grade Toggle and Decorator Rocker Switches, 15A 120V AC



Wiring	Toggle Switch					Decorator Switch			
	Push and Side Wired				Side Wire	Push, Back and Side Wired			
	Single Pole		3-Way		4-Way	Single Pole	Double Pole	3-Way	4-Way
Type	Grounding	Self-Grounding	Grounding	Self-Grounding	Self-Grounding	Self-Grounding	Self-Grounding	Self-Grounding	Self-Grounding
Black	RS115BK	—	RS315BK	—	—	RSD115BK	RSD215BK	RSD315BK	RSD415BK
Brown	RS115	RS115S	RS315	RS315S	RS415	RSD115	RSD215	RSD315	RSD415
Gray	—	—	—	—	—	RS115GY	RSD215GY	RSD315GY	RSD415GY
Ivory	RS115I	RS115SI	RS315I	RS315SI	RS415I	RSD115I	RSD215I	RSD315I	RSD415I
Lt. Almond	RS115LA	RS115SLA	RS315LA	RS315SLA	RS415LA	RSD115LA	RSD215LA	RSD315LA	RSD415LA
White	RS115W	RS115SW	RS315W	RS315SW	RS415W	RSD115W	RSD215W	RSD315W	RSD415W

Residential Grade Illuminated Toggle, Illuminated and Pilot Decorator Rocker Switches, 15A 120V AC



Wiring	Illuminated Toggle Switch, Frame is Clear and Illuminates, Toggle is Colored, Does Not Require a Neutral Wire		Illuminated Decorator, Illuminates when Switch is OFF, Does Not Require a Neutral Wire		Pilot Light Decorator, Illuminates when Switch is ON, Requires a Neutral Wire
	Push and Side Wired		Push, Back and Side Wired		Push, Back and Side Wired
	Self-Grounding		Self-Grounding		Self-Grounding
Type	Single Pole	3-Way	Single Pole	3-Way	Single Pole
Clear	RS115ILC	RS315ILC	—	—	—
Ivory	RS115ILI	RS315ILI	RSD115ILI	RSD315ILI	RSD115PLI
Lt. Almond	RS115ILLA	RS315ILLA	RSD115ILLA	RSD315ILLA	RSD115PLLA
White	RS115ILW	RS315ILW	RSD115ILW	RSD315ILW	RSD115PLW

Product Dimensions

Inches (mm)

	Toggle	Decorator
A	4.19" (106.5)	3.81" (96.8)
B	3.28" (83.3)	3.28" (83.3)
C	1.30" (33.0)	1.47" (37.3)
D	1.08" (27.4)	1.16" (29.6)
E	2.31" (58.7)	1.88" (47.7)

