

Locking Devices




Midget 15 Amp Locking Devices

Midget 15A 125V Locking Devices Inches (mm)



Rating	Poles/ Wires	Cord Diameter	Color	Nylon with Non-metallic Cord Grip, Plugs are Polarized		Flanged Devices Equipment Base with Nylon White Cup	
				Plug	Connector	Male	Female
NEMA ML1, 15A 125V	2-Pole 2-Wire	.220-.425" (5.6-10.8)	Black/White Black	7465N 7465NB	7464N* 7464NB*	7466N —	7468N* —





Note: *Will accommodate both polarized and nonpolarized plugs.
See page H-20 for weather protective boots for midget locking devices.

Midget 15A 125V and 125/250V Locking Devices Inches (mm)



Rating	Poles/ Wires	Cord Diameter	Color	Nylon with Quad Gripper® Cord Grip		Flanged Devices Equipment Base with Nylon White Cup	
				Plug	Connector	Male	Female
NEMA ML2, 15A 125V	2-Pole 3-Wire	.281"-.625" (7.1-15.9)	Black/White	7594NP	7593NC	7595MB	7596ER
NEMA ML3, 15A 125/250V	3-Pole 3-Wire	.281"-.625" (7.1-15.9)	Black/White	7485NP	7484NC	7486MB	7487ER



Note: See page H-20 for weather protective boots for midget locking devices.

Product Dimensions Inches (mm)

Plug	Connector
A 1.60" (40.6)	2.15" (54.6)
B 1.12" (28.4)	1.12" (28.4)
C 1.25" (31.8)	1.25" (31.8)

	Flanged Devices		
	7466N	7468N	MB/ER Series
A	1.63" (41.4)	1.63" (41.4)	2.06" (52.3)
B	1.38" (35.1)	1.38" (35.1)	1.75" (44.5)
C	1.08" (27.4)	0.95" (24.1) O.D.	1.62" (41.1)
D	1.19" (30.2)	1.09" (27.7)	1.23" (31.2)
E	0.09" (2.3)	0.09" (2.3)	1.17" (29.7)

