

Weatherproof Non-Metallic Recessed While-In-Use Extra Duty Covers

Bryant has added a unique solution to our weatherproof, non-metallic device cover line up with the Recessed In-Use Extra Duty rated Cover. This is a great alternative for locations to meet the NEC code when space and aesthetics are important.

- Aesthetically pleasing flat profile
- Meets the Extra Duty rating
- Versatility, it can be installed for new or old work
- Compatibility with all common siding types and materials: vinyl, wood, stucco and brick/block
- Mounted horizontally or vertically
- Includes an electrical box and optional siding flange
- Compatibility with duplex, GFCI and single receptacles (receptacle not included)
- cULus listed product and NEC and NEMA 3R compliant
- Colors available clear cover with gray, white or bronze back housing



RW5420CW

Non-Metallic EXTRA DUTY® While-In-Use Covers

Description	Color	Catalog Number
1-Gang Weatherproof Extra Duty Recessed While-In-Use Cover	Clear/Gray	RW5420CG
	Clear/White	RW5420CW
	Clear/Bronze	RW5420CZ

Weatherproof Heavy Cast Aluminum Lockable Cover

Made of heavy cast aluminum that provides high strength. Suitable for industrial and commercial applications.

- Flush enclosure, cover has mounting plate, fits standard 4-Inch or 4 1/16 electrical box
- Adapter plates for GFCI, duplex, single receptacles or switch
- Rated NEMA 3R
- cULus listed



WP4600

Weatherproof Heavy Cast Aluminum Lockable Cover

Description	Color	Catalog Number
1-Gang weatherproof 4 in 1 flush enclosure heavy cast aluminum lockable cover.	Aluminum	WP4600