



Features and Benefits

- High impact-resistant thermoplastic frame
- Meets FCC part 68
- UL Listed 1863 – Communication Circuit Accessory and CSA Certified

Molded-In Voice and Data Decorator Frames



| | | | 2 Jack Voice Data Frame | |
|--------------|----------------|----------------|-------------------------|------------------------------|
| Jack | One RJ11 Jack | One RJ11 Jack | Duplex RJ11 Jack | RJ11 Jack Category 5e |
| Position | 6-Position | 6-Position | 6-Position | 6-Position 8-Position |
| Conductors | 4-Conductor | 6-Conductor | 6-Conductor | 4-Conductor 8-Conductor |
| Terminations | Screw | Screw | Screw | Screw 110 IDC |
| Black | NS770BK | – | – | NS784BK |
| Brown | NS770 | NS771 | – | NS784 |
| Gray | NS770GY | – | – | NS784GY |
| Ivory | NS770I | NS771I | NS772I | NS784I |
| Light Almond | NS770LA | NS771LA | NS772LA | NS784LA |
| White | NS770W | NS771W | NS772W | NS784W |

Molded-In Video and Voice Decorator Frames



| | | | | |
|--------------|--------------------------------|--------------------------------|--|-----------------------------|
| Jack | | | One RJ11 Jack, 6-Position, 4-Conductor | One Cat 5e 110 Punch-Down |
| F-Connector | Single F-Type Coupler Bulkhead | Duplex F-Type Coupler Bulkhead | One F-Type Coupler Bulkhead | One F-Type Coupler Bulkhead |
| Type | Female to Female | Female to Female | Female to Female | Female to Female |
| Terminations | Screw | Screw | Screw | Screw |
| Black | – | – | – | NS785BK |
| Brown | – | – | – | NS785 |
| Gray | – | – | – | NS785GY |
| Light Almond | NS780LA | – | NS783LA | NS785LA |
| White | NS780W | NS782W | NS783W | NS785W |

Note: Standard plates available; see section Q.