

# Network Wiring

## In-Wall AV Delivery

netSELECT®



- High density delivery of power, data and AV
- Stud or sheetrock mounting flexibility
- Steel construction for residential MDU and commercial applications
- Easily reconfigured to adapt to new applications



### FPTV Connection Enclosure Inches (mm)

Description	Dimensions			Catalog Number
	Height	Width	Depth	
2-Gang in-wall enclosure	8.16" (207)	7.92" (201)	3.37" (86)	<b>NSAV62M</b>
Steel cover for NSAV6 series	7.2" (183)	7.2" (183)	0.05" (1)	<b>NSAV6C</b>
Block wall adapter				<b>NSAV6BW</b>
New work stud brackets				<b>NSAV6NW</b>

### Power Kits

Description	Color	Catalog Number
Standard power kit, includes wallplate, box and 15A tamper-resistant outlet	White	<b>NSOKPTR</b>
Surge protected power kit, includes wallplate, box and surge protected outlet	Blue	<b>NSOKPS</b>



### HDMI Frames

Description	Color	15A 125V, Tamper-Resistant Duplex Receptacle	
		1-Gang, 1-Port	1-Gang, 2-Port
HDMI, decorator frame, female to female	Almond	<b>NS801AL</b>	<b>NS802AL</b>
	Black	<b>NS801BK</b>	<b>NS802BK</b>
	Gray	<b>NS801GY</b>	<b>NS802GY</b>
	Ivory	<b>NS801I</b>	<b>NS802I</b>
	Light Almond	<b>NS801LA</b>	<b>NS802LA</b>
	White	<b>NS801W</b>	<b>NS802W</b>

### Recessed Receptacles

Color	15A 125V, Tamper-Resistant Duplex Receptacle		
	1-Gang	2-Gang with Feed-Through	2-Gang with Snap Fit
Ivory	<b>RR1510I</b>	<b>RR1512I</b>	<b>RR1514I</b>
Light Almond	<b>RR1510LA</b>	<b>RR1512LA</b>	<b>RR1514LA</b>
White	<b>RR1510W</b>	<b>RR1512W</b>	<b>RR1514W</b>

### Feed-Through Plates

Color	1-Gang	2-Gang
Ivory	<b>NSAV11*</b>	<b>NSAV21*</b>
White	<b>NSAV1W*</b>	<b>NSAV2W*</b>

Note: \*Not UL Listed.



### Two and Three Gangable AV Wallboxes Inches (mm)

Box	Dimensions			Top Knockouts	Bottom Knockouts	Back Knockouts	Catalog Number
	Height	Width	Depth				
2-Gang, 2" KO, 54 in <sup>3</sup> capacity	4.21" (107)	4.06" (103)	4.0" (102)	(2) 1/2" (2) 1/2" - 3/4" TKO*	(1) 1", 1 1/4", 1 1/2" and 2"	(2) 1/2" - 3/4" TKO	<b>HBL985</b>
3-Gang, 2" KO, 79 in <sup>3</sup> capacity	4.21" (107)	5.87" (149)	4.0" (102)	(3) 1/2" (3) 1/2" - 3/4" TKO*	(1) 1/2", (1) 1/2" - 3/4" TKO* (1) 1", 1 1/4", 1 1/2" and 2"	(3) 1/2" - 3/4" TKO	<b>HBL986</b>

Note: \*TKO (Tangential Knockout).

### Wallbox

Description	Color	Catalog Number
2-Gang, nail-on box, thermoplastic	Blue	<b>RR1500</b>

### Low Voltage AV Wallbox Partitions

Compatible With	Description	Quantity	Catalog Number
HBL985 and HBL986	Solid divider	1	<b>HBL989</b>
	With pass-thru capability	1	<b>HBL989AVD</b>