

Kellems® Wire Management Products

90° Male Cord Connectors

Form Size 1-6



UL Listed to Type 4,
4X, 12 and Type 13

IP66*
SUITABILITY



90° Male

N.P.T. Hub Size	Cord Diameter Inches (mm)	Form Size	Color Code	Machined Aluminum†	Machined Zinc-Plated Steel ^Δ	Nylon Gray	Nylon Black	Cast Aluminum
3/8	.25"-.31" (6.3-7.9)	F1	Black	NHC1010	—	—	—	—
	.31"-.38" (7.9-9.5)		White	NHC1011	—	—	—	—
	.38"-.44" (9.5-11.0)		Blue	NHC1012	—	—	—	—
1/2	.06"-.13" (1.6-3.2)	F2	Green	—	—	—	—	—
	.13"-.19" (3.2-4.7)		Orange	NHC1020	—	NHC1020CR	—	—
	.19"-.25" (4.7-6.3)		Red	NHC1021	NHC1021ZP	NHC1021CR	—	—
	.25"-.38" (6.3-9.7)		White	NHC1022	NHC1022ZP	NHC1022CR	NHC2022CR	—
	.38"-.50" (9.7-12.7)		Blue	NHC1023	NHC1023ZP	NHC1023CR	NHC2023CR	—
	.50"-.63" (12.7-15.9)		Brown	NHC1024**	NHC1024ZP**	NHC1024CR**	NHC2024CR**	—
3/4	.38"-.50" (9.7-12.7)	F3	Blue	NHC1035	NHC1035ZP	NHC1035CR	—	—
	.50"-.63" (12.7-15.9)		Brown	NHC1036	NHC1036ZP	NHC1036CR	—	—
	.63"-.75" (15.9-19.0)		Yellow	NHC1037	NHC1037ZP	NHC1037CR	—	—
	.75"-.88" (19.0-22.2)		Orchid	NHC1038	NHC1038ZP	NHC1038CR	—	—
1	.50"-.63" (12.7-15.9)	F4	Brown	NHC1040	—	—	—	—
	.63"-.75" (15.9-19.0)		Yellow	NHC1041	NHC1041ZP	NHC1041CR	NHC2041CR	—
	.75"-.88" (19.0-22.2)		Orchid	NHC1042	—	NHC1042CR	NHC2042CR**	—
	.88"-1.00" (22.2-25.4)		Gray	NHC1043**	—	NHC1043CR	NHC2043CR**	—
	1.00"-1.13" (25.4-28.7)		Pink	NHC1044**	—	—	—	—
1 1/4	.88"-1.00" (22.2-25.4)	F5	—	—	—	—	—	NHC1051
	1.00"-1.13" (25.4-28.6)		—	—	—	—	—	NHC1052
	1.13"-1.25" (28.6-31.7)		—	—	—	—	—	NHC1053**
	1.25"-1.38" (31.7-34.9)		—	—	—	—	—	NHC1054**
1 1/2	1.00"-1.13" (25.4-28.6)	F5	—	—	—	—	—	NHC1057
	1.13"-1.25" (28.6-31.7)		—	—	—	—	—	—
	1.25"-1.38" (31.7-34.9)		—	—	—	—	—	NHC1059
2	1.38"-1.50" (34.9-38.1)	F6	—	—	—	—	NHC1066	

Note: See pages T-92 to T-101 for additional technical data and dimensional drawings.

* IP66 Suitability when used with optional metal clad O-ring shown on page T-89.

** Cable jacket may have to be stripped to pass through connector body.

† Nuts are machined aluminum and bodies are cast aluminum.

Δ Compression nuts are machined zinc-plated steel and bodies are zinc-plated malleable iron. Locknuts sold separately. See page T-89.



Machined Aluminum[†]



Machined Zinc-Plated Steel^Δ



Gray Nylon



Black Nylon



Cast Aluminum