









Duplex Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number
 1-Gang, 1-Duplex	Almond	NP8AL	NPJ8AL	-	Aluminum	SA8
	Black	NP8BK	NPJ8BK	-	Brass	SB8
	Blue	-	NPJ8BL	-	Brass Plated	SBP8
	Brown	NP8	NPJ8	-	Chrome	SCH8
	Gray	NP8GY	NPJ8GY	-	S/S 302/304	SS8
	Ivory	NP8I	NPJ8I	NPJJ8I	S/S 430	SS8L
	Light Almond	NP8LA	NPJ8LA	NPJJ8LA	Steel, Almond	SP8AL*
	Office White	NP8OW	NPJ8OW	-	Steel, Gray	SP8G*
	Orange	NP8OR	-	-		
	Red	NP8R	NPJ8R	-		
	White	NP8W	NPJ8W	NPJJ8W		
	 2-Gang, 2-Duplex	Black	NP82BK	NPJ82BK	-	Aluminum
Brown		NP82	NPJ82	-	Brass	SB82
Gray		NP82GY	NPJ82GY	-	Brass Plated	SBP82
Ivory		NP82I	NPJ82I	-	Chrome	SCH82
Light Almond		NP82LA	NPJ82LA	-	S/S 302/304	SS82
Office White		NP82OW	NPJ82OW	-	S/S 430	SS82L
Orange		NP82OR	-	-	Steel, Almond	SP82AL*
Red		NP82R	NPJ82R	-	Steel, Gray	SP82G*
White		NP82W	NPJ82W	-		
 3-Gang, 3-Duplex	Brown	NP83	-	-	Aluminum	①
	Ivory	NP83I	-	-	Brass	①
	White	NP83W	-	-	Brass Plated	①
					Chrome	①
				S/S 302/304	SS83	
				S/S 430	-	
				Steel, Almond	SP83AL*	
 4-Gang, 4-Duplex	Brown	NP84	-	-	Aluminum	①
	Ivory	NP84I	-	-	Brass	①
	White	NP84W	-	-	Brass Plated	①
					Chrome	①
				S/S 302/304	SS84	
				S/S 430	-	
 2-Gang, 1-Duplex	Brown	-	-	-	Brass	-
	Ivory	-	-	-	Brass Plated	-
	White	-	-	-	Chrome	-
					S/S 302/304	SS748
				S/S 430	-	

Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number
 1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Black	NP7BK	NPJ7BK	-	Aluminum	SA7
	Brown	NP7	NPJ7	-	Brass	SB7
	Gray	NP7GY	NPJ7GY	-	Brass Plated	SBP7
	Ivory	NP7I	NPJ7I	-	Chrome	SCH7
	Light Almond	NP7LA	NPJ7LA	-	S/S 302/304	SS7
	Office White	NP7OW	NPJ7OW	-	S/S 430	SS7L
	Red	NP7R	NPJ7R	-	Steel, Almond	SP7AL*
	White	NP7W	NPJ7W	-	Steel, Gray	SP7G*
 2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Brown	-	-	-	Aluminum	-
	Ivory	-	-	-	Brass	-
	White	-	-	-	Brass Plated	-
					Chrome	-
				S/S 302/304	SS747	
				S/S 430	-	
 2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole	Brown	-	-	-	Aluminum	①
	Ivory	-	-	-	Brass	①
	White	-	-	-	Brass Plated	①
					Chrome	①
					S/S 302/304	SS72
				S/S 430	-	

Note: All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

①vA available as a custom wallplate, see pages N-31 to N-34. Consult custom wallplates section for additional openings and combinations.

*Powder coat paint finish.

Dimensions in Inches (mm)