

# Network Wiring and netSELECT® Products

## AV 110 Everywhere™ Analog AV Over UTP

### Tamper-Resistant Receptacle with 5V DC Power Output

Description	Color	Catalog Number
USB charger	Black	<b>AVPS15BK</b>
TR receptacle,	Ivory	<b>AVPS15I</b>
(1) USB port 3A,	Gray	<b>AVPS15GY</b>
switched 5V DC output,	Office White	<b>AVPS15LA</b>
15A, 125V AC	White	<b>AVPS15W</b>
decorator duplex		



### USB 2.0 High Speed 110 Extenders, 100ft

Description	Color	1.5 Unit Module
4-pair UTP cable	Black	<b>IMU11015BK</b>
installation, up to	Ivory	<b>IMU11015EI</b>
100ft (305m)	Gray	<b>IMU11015GY</b>
	Office White	<b>IMU11015OW</b>
	White	<b>IMU11015W</b>

Note: Product consists of send and receive pair.



### HDMI 1080P 110 UTP Extenders

(2) 4-pair UTP cable installation, 5V DC, up to 147ft (45m)

Color	Decorator	2 Unit Module
Black	<b>ISFH110BK</b>	<b>IMH110ST2BK</b>
Ivory	<b>ISFH110EI</b>	<b>IMH110ST2EI</b>
Gray	<b>ISFH110GY</b>	<b>IMH110ST2GY</b>
Office White	<b>ISFH110OW</b>	<b>IMH110ST2OW</b>
White	<b>ISFH110W</b>	<b>IMH110ST2W</b>

Note: Product consists of send and receive pair.



### VGA and 3.5mm HD AV Extender

Extend up to 75ft (23m) over two 4-pair UTP cables, 1.5 unit

Color	Catalog Number
Black	<b>IM15311015BK</b>
Gray	<b>IM15311015GY</b>
Ivory	<b>IM15311015EI</b>
Office White	<b>IM15311015OW</b>
White	<b>IM15311015W</b>

Note: Product consists of send and receive pair.



### RCA Component with Audio 110 Audio/Video Modules

Extend up to 75ft (23m) over (2) 4-pair UTP cables, 1.5 unit

Color	RCA Component Video, Left/Right Audio	RCA Component Video, 3.5mm Audio
Black	<b>IMCAR11015BK</b>	<b>IMC3511015BK</b>
Gray	<b>IMCAR11015GY</b>	<b>IMC3511015GY</b>
Ivory	<b>IMCAR11015EI</b>	<b>IMC3511015EI</b>
Office White	<b>IMCAR11015OW</b>	<b>IMC3511015OW</b>
White	<b>IMCAR11015W</b>	<b>IMC3511015W</b>



### RCA 110 Audio/Video Modules

Extend up to 100ft (30.5m) over (1) 4-pair UTP cables, 1 unit

Color	75ft (23m) max.	100ft (30.5m) max.	
	RCA Component Video, HD	RCA Composite Video, Left/Right Audio	RCA Left/Right Audio
Black	<b>IMCR1101BK</b>	<b>IMR1101BK</b>	<b>IMAR1101BK</b>
Gray	<b>IMCR1101GY</b>	<b>IMR1101GY</b>	<b>IMAR1101GY</b>
Ivory	<b>IMCR1101EI</b>	<b>IMR1101EI</b>	<b>IMAR1101EI</b>
Office White	<b>IMCR1101OW</b>	<b>IMR1101OW</b>	<b>IMAR1101OW</b>
White	<b>IMCR1101W</b>	<b>IMR1101W</b>	<b>IMAR1101W</b>