

## Universal Patch Panels and Wall Mount Brackets



### Consolidation Point Block, Category 6 and Category 5e

Description	Catalog Number
Category 6, 12-Port, Universal, 89D.	<b>HP612</b>
Category 5e, 12-Port, Universal, 89D.	<b>HP5E12</b>

### Universal Patch Panel, Category 5e

Description	Catalog Number
24-Port, 1.75" H.	<b>HP5E24</b>
48-Port, 3.50" H.	<b>HP5E48</b>
96-Port, 7.0" H.	<b>HP5E96</b>



### Universal Patch Panel, Category 6

Description	Catalog Number
24-Port, 1.75" H.	<b>HP624</b>
48-Port, 3.50" H.	<b>HP648</b>
96-Port, 7.0" H.	<b>HP696</b>



### Jack Panel, Unloaded

Description	Catalog Number
Wall Mount, 12-Port, Black.	<b>HPJ1289</b>
Rack Mount, 24-Port, 1.75" H, Black.	<b>NSPJ24</b>
Rack Mount, 48-Port, 3.5" H, Black.	<b>NSPJ48</b>



### Rear Cable Management Bar\*

Description	Catalog Number
Screws to the rear flange of a 19-inch rack.	<b>CMBR</b>
HPW panel mount.	<b>HPRCMB</b>



Note: \*Not UL Listed.



### Wall Mount Brackets, Bottom-Hinged

Includes assembled bottom-hinged wall bracket.

Rack Units	Width Inches (mm)	Depth Inches (mm)	Height Inches (mm)	Catalog Number
1	19" (483)	4" (102)	1.75" (45)	<b>HPWWB1U4</b>
2	19" (483)	4" (102)	3.50" (89)	<b>HPWWB2U4</b>
		8" (203)	3.50" (89)	<b>HPWWB2U8</b>
4	19" (483)	4" (102)	7.00" (178)	<b>HPWWB4U4</b>
		8" (203)	7.00" (178)	<b>HPWWB4U8</b>
		4" (102)	10.50" (267)	<b>HPWWB6U4</b>
6	19" (483)	8" (203)	10.50" (267)	<b>HPWWB6U8</b>
		8" (203)	10.50" (267)	<b>HPWWB6U8</b>
		18" (457)	10.50" (267)	<b>HPWWB6U18</b>



### Wall Mount Brackets, Side-Hinged

Includes assembled side-hinged wall bracket.

Rack Units	Width Inches (mm)	Depth Inches (mm)	Height Inches (mm)	Catalog Number
2	19" (483)	4" (102)	3.50" (89)	<b>BRMCCMB19X35X4</b>
4	19" (483)	4" (102)	7.00" (178)	<b>BRMCCMB19X7X4</b>
2	19" (483)	8" (203)	3.50" (89)	<b>BRMCCMB19X35X8</b>
4	19" (483)	8" (203)	7.00" (178)	<b>BRMCCMB19X7X8</b>

