

Combination Switches/Devices

Features

Mini-toggles provide for multiple switches in a compact single gang. Maximize control while maintaining function and appearance.

- Low profile, less than 1 inch
- Self-grounding feature is standard
- Combination devices provide compact switches in a single-gang opening
- Smooth toggle action
- Multiple-drive Slot/Phillips/Robertson head screws
- Hi-visibility yellow base for easy installation
- Operating temperature: -20°C to 60°C
- UL Listed, CSA Certified



RC108I

Combination Toggle Switches/Devices

| Description | Two (2) Single Pole Switches | Single Pole Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle | Single Pole Switch, 2 Pole, 3 Wire, Receptacle | Single Pole Switch, Pilot Light, Clear Lens, Amber Neon Bulb* |
|--------------|------------------------------|--|---|---|
| Termination | Self-Grounding, Side Wire | Self-Grounding, Side Wire | Self-Grounding, Side Wire | Self-Grounding, Side Wire |
| Rating | 15A 120V AC | 15A 120V (switch) 15A 125V (recept.) NEMA 5-15R | 15A 120V (switch) 15A 125V (recept.) NEMA 5-15R | 15A 120V AC |
| Color | | | | |
| Brown | RC101 | RC108TR | RC108 | RC109 |
| Ivory | RC101I | RC108ITR | RC108I | RC109I |
| Light Almond | RC101LA | RC108LATR | RC108LA | RC109LA |
| White | RC101W | RC108WTR | RC108W | RC109W |

Note: See page Tech-10 for Tamper-Resistant description.
*Neutral required for pilot light, see page X-4 for wiring diagram.

Combination Toggle Switches/Devices

| Description | Single Pole and Three Way Switch | Two (2) Three Way Switches | Three Way Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle | Three Way Switch, 2 Pole, 3 Wire, Receptacle | Three Way Switch, Pilot Light, Clear Lens, Amber Neon Bulb* |
|--------------|----------------------------------|----------------------------|--|---|---|
| Termination | Self-Grounding, Side Wire | Self-Grounding, Side Wire | Self-Grounding, Side Wire | Self-Grounding, Side Wire | Self-Grounding, Side Wire |
| Rating | 15A 120V AC | 15A 120V AC | 15A 120V (switch) 15A 125V (recept.) NEMA 5-15R | 15A 120V (switch) 15A 125V (recept.) NEMA 5-15R | 15A 120V AC |
| Color | | | | | |
| Brown | RC103 | RC303 | RC308TR | RC308 | RC309 |
| Ivory | RC103I | RC303I | RC308ITR | RC308I | RC309I |
| Light Almond | RC103LA | RC303LA | RC308LATR | — | — |
| White | RC103W | RC303W | RC308WTR | RC308W | RC309W |

Note: See page Tech-10 for Tamper-Resistant description.
*Neutral required for pilot light, see page X-4 for wiring diagram.

Dimensions in Inches (mm)