

# Locking Devices

## 50 Amp Plugs, Connectors, Flanged Devices and Receptacles

50A 125V, 250V, 480V, 125/250V, 3Ø 250V AC and 3Ø 480V AC Locking Devices, 2-Pole 3-Wire and 3-Pole 4-Wire Grounding Inches (mm)



Rating	Poles/Wires	Cord Diameter	Description	Plug	Connector	Flanged Devices		Single Armored Receptacle
						Male	Male with Cover	
50A 125/250V AC Plug Connector	3-Pole	.65"-1.20"	Black Nylon	<b>CS6365L</b>	<b>CS6364L</b>	<b>CS6375L</b>	<b>CS6375LC</b>	<b>CS6369L</b>
	4-Wire	(16.5-30.5)						
	3-Pole	.830"-1.250"	Heavy Duty Black	<b>CS6365</b>	<b>CS6364</b>	—	—	<b>CS6369A</b>
	4-Wire	(21.1-31.8)	Steel Casing	—	—	<b>CS6375A</b>	—	—
50A 3Ø 250V AC Plug Connector	3-Pole	.65"-1.20"	Black Nylon	<b>CS8365L</b>	<b>CS8364L</b>	<b>CS8375L</b>	<b>CS8375LC</b>	<b>CS8369L</b>
	4-Wire	(16.5-30.5)						
	3-Pole	.830"-1.250"	Heavy Duty Black	<b>CS8365</b>	<b>CS8364</b>	—	—	<b>CS8369A</b>
	4-Wire	(21.1-31.8)	Steel Casing	—	—	<b>CS8375A</b>	—	—
			Steel Casting with Weatherproof Cover Plate	—	—	<b>CS8375MBWP</b>	—	—
50A 3Ø 480V AC Plug Connector	3-Pole	.830"-1.250"	Heavy Duty Black	<b>CS8165</b>	<b>CS8164</b>	—	—	<b>CS8169A</b>
	4-Wire	(21.1-31.8)	Steel Casing	—	—	<b>CS8175A</b>	—	—
50A 125V AC Plug Connector	2-Pole	.830"-1.250"	Heavy Duty Black	<b>CS6361</b>	<b>CS6360</b>	<b>CS6377A</b>	—	<b>CS6370A</b>
	3-Wire	(21.1-31.8)						
50A 250V AC Plug Connector	2-Pole	.830"-1.250"	Heavy Duty Black	<b>CS8265</b>	<b>CS8264</b>	<b>CS8275A</b>	—	<b>CS8269A</b>
	3-Wire	(21.1-31.8)						
50A 480V AC Plug Connector	2-Pole	.830"-1.250"	Heavy Duty Black	<b>CS8465</b>	<b>CS8464</b>	<b>CS8475A</b>	—	<b>CS8469A</b>
	3-Wire	(21.1-31.8)						

Note: See page G-23 for weather protective boots and accessories.

### Product Dimensions Inches (mm)

	Plug		Single Receptacle		Flanged Devices	
	CS6365L	CS6365	CS6369L	CS6369	CS6375L	CS6375
A	5.80" (147)	6.38 (162.1)	3.30" (84.0)	3.28" (83.3)	—	3.50" (88.9)
B	2.40" (61)	2.56 (65.0)	2.70" (69.0)	—	2.10" (53.0)	2.12" (53.8)
			2.10" (53.0)	2.12" (53.8)	2.70" (69.0)	2.77" (70.4)
			2.40" (61.0)	2.44" (62.0)	2.20" (56.0)	2.17" (55.1)
			1.10" (25.0)	1.03" (26.2)	0.19" (4.8)	0.19" (4.8)
			2.10" (53.0)	2.69" (68.3)	—	—
			—	0.62" (15.7)	—	—

