

# Painted Metal Plates and Thermoplastic Communication Frames



## Painted Metal Plates<sup>(1)</sup> Inches (mm)

Color	Gang	Switch	Duplex	Rectangular	Blank		Single Receptacle, 1.40" (35.6) Dia. Hole
					Box Mount	Strap Mount	
Almond	1	<b>SP1AL</b>	<b>SP8AL</b>	<b>PHPS1AL</b>	<b>SP14BAL</b>	<b>SP14AL</b>	<b>SP7AL</b>
	2	<b>SP2AL</b>	<b>SP82AL</b>	<b>PHPS2AL</b>	<b>SP24BAL</b>	<b>SP24AL</b>	—
	3	<b>SP3AL</b>	<b>SP83AL</b>	<b>PHPS3AL</b>	<b>SP34BAL</b>	<b>SP34AL</b>	—
	4	<b>SP4AL</b>	—	<b>PHPS4AL</b>	—	—	—
	5	<b>SP5AL</b>	—	<b>PHPS5AL</b>	—	—	—
	6	<b>SP6AL</b>	—	<b>PHPS6AL</b>	—	—	—
Gray	1	<b>SP1G</b>	<b>SP8G</b>	<b>PHPS1G</b>	<b>SP14BG</b>	<b>SP14G</b>	<b>SP7G</b>
	2	<b>SP2G</b>	<b>SP82G</b>	<b>PHPS2G</b>	<b>SP24BG</b>	<b>SP24G</b>	—

## Painted Metal Combination Plates<sup>(1)</sup>



Color	Gang	1-Toggle, 1-Duplex	1-Toggle, 1-Decorator	Gang	2-Toggle, 1-Duplex	2-Toggle, 1-Decorator
Gray	2	<b>SP18G</b>	<b>PJS126G</b>	3	<b>SP28G</b>	<b>PJS226G</b>

## Thermoplastic Communication Frames<sup>(1)</sup> Inches (mm)



Color	Gang	2-Port Decorator Frame	3-Port Decorator Frame	4-Port Decorator Frame	6-Port Decorator Frame	Decorator, .41" (10.3) Dia. Hole	Decorator, Blank
Gray	1	<b>NS612GY</b>	<b>NS613GY</b>	<b>NS614GY</b>	<b>NS616GY</b>	—	<b>NS620GY</b>

Note: <sup>(1)</sup> Almond devices and plates match ivory metal raceway.  
 Bryant's Audio/Video Connectors allow custom creation of multimedia outlets and workstations while maintaining a decorative look.  
 See Network Wiring Section Q for more information.