

Power System Distribution Assemblies

LINKOSITY® Feed - UL Type 3R Rated*

3R Rated Standard Items

Description	Catalog Number
20A 125V Ground Fault	M3R002SGGF0
20A 125V Switched, Spec Grade	M3RSL1SG000
20A 125V Switched, Ground Fault	M3RSL1SGGF0
20A 125V Spec Grade	M3R002SG000
20A 125V Ground Fault, Pass-Thru	M3R002SGGF0P
20A 125V Switched, Spec Grade, Pass-Thru	M3RSL1SG00P
20A 125V Switched, Ground Fault Pass-Thru	M3RSL1SGGF0P
Spec Grade, Pass-Thru	M3R002SG00P

Note: *When cover closed.
Accepts PH2304 series cables.



Device Type	Style	Type	No. of Devices	Device Type	Device Feature	Pass-Thru
M	3R - 3R Lids 3D - 3R Deep Cover	SL - Switch Local	1	SG - Spec Grade	IG - Isolated Ground	P - Pass-Thru
		SM - Switch Master	2	HG - Hospital Grade	GF - Ground Fault	O - No Pass-Thru
		00 - None		CR - Corrosion Resistant	SI - Surge/IG	
				L1 - 15A Locking	SS - Surge	
					00 - Standard	



LINKOSITY® Feed - UL Type 4X Rated*

4X Rated NEMA Standard Items

Description	Catalog Number
20A 125V Straight Blade	MLWF2010
20A 125V WTSSTL	MLWF2020
20A 125V Straight Blade, Pass-Thru	MLWF201P
20A 125V WTSSTL, Pass-Thru	MLWF202P

Note: *Watertight Safety-Shroud® Twist-Lock® Plug required when in use.
**Straight Blade are UL Type 4X when not in use only.
WTSSTL is an abbreviation for Watertight Safety-Shroud® Twist-Lock®.
Accepts PH2304 series cables.

Device Type	Style	Type	No. of Devices	Device Type	Pass-Thru
M	L - LINKOSITY	WF - Watertight Safety-Shroud Receptacle	2	01 - 20A 125V Straight Blade**	P - Pass-Thru
		WM - Watertight Safety-Shroud Inlet		02 - 20A 125V Twist-Lock	O - No Pass-Thru
				03 - 20A 250V Twist-Lock	
				04 - 20A 277V Twist-Lock	
				05 - 30A 125V Twist-Lock	
				06 - 30A 250V Twist-Lock	
				07 - 20A 125/250V Twist-Lock	
				08 - 20A 3Ø 250V Twist-Lock	
				09 - 20A 3Ø 480V Twist-Lock	
				10 - 30A 125/250V Twist-Lock	
				11 - 30A 3Ø 250V Twist-Lock	
				12 - 30A 3Ø 480V Twist-Lock	
				13 - 30A 3Ø 600V Twist-Lock	



All LINKOSITY® - UL Type 4X Rated*

4X Rated LINKOSITY Standard Items

Description	Catalog Number
20A 3W up to 600V, 4 Port	M4L2003PB0
20A 3W up to 600V, 4 Port Pass-Thru	M4L2003PBP

Note: *Closure Cap required when not in use.
Accepts PH2304 series cables.

Device Type	Style	Type	No. of Poles	Conductor Colors	Pass - Thru
M	4L - LINKOSITY	20 - 20A	02	PA - Green/Yellow Black (all others)	P - Pass-Thru
		23 - 20A Super Neutral Isolated Ground	03 04 05 06	PB - Green/Yellow White Black (all others)	O - No Pass-Thru
		30 - 30A			

Conduit Feed - UL Type 4X Rated*

Conduit Feed Standard Items

Description	Catalog Number
20A 125V Straight Blade	MCWF2010
20A 125V WTSSTL	MCWF2020
20A 250V WTSSTL	MCWF2030
20A 277V WTSSTL	MCWF2040
30A 125V WTSSTL	MCWF2050
30A 250V WTSSTL	MCWF2060
20A 125/250V WTSSTL	MCWF2070
20A 3Ø, 250V WTSSTL	MCWF2080
20A 3Ø, 480V WTSSTL	MCWF2090
30A 125/250V WTSSTL	MCWF2100
30A 3Ø 250V WTSSTL	MCWF2110
30A 3Ø 480V WTSSTL	MCWF2120
30A 3Ø 600V WTSSTL	MCWF2130

Note: *Watertight Safety-Shroud® Twist-Lock® Plug required when in use.
WTSSTL is an abbreviation for Watertight Safety-Shroud® Twist-Lock®.

Device Type	Style	Type	No. of Devices	NEMA Device Type	Pass-Thru
M	C - Conduit Feed	WF - Watertight Safety-Shroud Receptacles	2	01 - 20A 125V Straight Blade	O - No Pass-Thru
		WM - Watertight Safety-Shroud Inlet		02 - 20A 125V Twist-Lock	
				03 - 20A 250V Twist-Lock	
				04 - 20A 277V Twist-Lock	
				05 - 30A 125V Twist-Lock	
				06 - 30A 250V Twist-Lock	
				07 - 20A 125/250V Twist-Lock	
				08 - 20A 3Ø 250V Twist-Lock	
				09 - 20A 3Ø 480V Twist-Lock	
				10 - 30A 125/250V Twist-Lock	
				11 - 30A 3Ø 250V Twist-Lock	
				12 - 30A 3Ø 480V Twist-Lock	
				13 - 30A 3Ø 600V Twist-Lock	



Replacement Mounting Feet

Description	Catalog Number
For Power Distribution Assemblies.	HBLRFT1^A

Note: ^A Package of 10 mounting feet and 10 screws.

