

Choose the appropriate configuration from the Selector below.

Hubbell Logic Configurator

For example, catalog number **HCMA05212** is derived as follows:

DEVICE TYPE	COUPLING NUT MATERIAL	BODY STYLE	POLES	CONDUCTOR TYPE	CABLE LENGTH (ft)
HC = Plug, Female HP = Plug, Male HI = Plug, Male Inline♦ HE = Male/Female Extension Cable♦ HJ = Male/Female Jumper Cable	M = Metallic N = Nylon	A = Right Angle S = Straight	02 03 04 05 06	1 = #16 AWG SEOOW Cable 3 = #18 AWM2661 IEC Cable* 4 = #18 AWG SEOOW Cable <i>*3 - 5 Pole Only</i>	** 03 06 12 20 <i>**Replace with Length</i>
HC	M	A	05	2	12

Note: Availability of specific items may vary. Consult factory for delivery. Consult the factory for additional cable lengths or cable types.
♦ Available with metallic coupling nut only.

2 - 6 Pole Plugs

Catalog numbers using #16 AWG SEOOW cable are listed below. For #18 AWG SEOOW or #18 AWM2661 IEC cable, change the conductor type per the Hubbell Logic chart above.

Poles	Male Face Shown Female - mirror image	Cable Length	Female Plugs		Male Plugs		Male/Female JumperCables
			Straight	Right Angle	Straight	Right Angle	Straight
2		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	HCMS02103	HCMA02103	HPMS02103	HPMA02103	HJMS02103
			HCMS02106	HCMA02106	HPMS02106	HPMA02106	HJMS02106
			HCMS02112	HCMA02112	HPMS02112	HPMA02112	HJMS02112
			HCMS021**	HCMA021**	HPMS021**	HPMA021**	HJMS021**
3		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	HCMS03103	HCMA03103	HPMS03103	HPMA03103	HJMS03103
			HCMS03106	HCMA03106	HPMS03106	HPMA03106	HJMS03106
			HCMS03112	HCMA03112	HPMS03112	HPMA03112	HJMS03112
			HCMS031**	HCMA031**	HPMS031**	HPMA031**	HJMS031**
4		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	HCMS04103	HCMA04103	HPMS04103	HPMA04103	HJMS04103
			HCMS04106	HCMA04106	HPMS04106	HPMA04106	HJMS04106
			HCMS04112	HCMA04112	HPMS04112	HPMA04112	HJMS04112
			HCMS041**	HCMA041**	HPMS041**	HPMA041**	HJMS041**
5		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	HCMS05103	HCMA05103	HPMS05103	HPMA05103	HJMS05103
			HCMS05106	HCMA05106	HPMS05106	HPMA05106	HJMS05106
			HCMS05112	HCMA05112	HPMS05112	HPMA05112	HJMS05112
			HCMS051**	HCMA051**	HPMS051**	HPMA051**	HJMS051**
6		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	HCMS06103	HCMA06103	HPMS06103	HPMA06103	HJMS06103
			HCMS06106	HCMA06106	HPMS06106	HPMA06106	HJMS06106
			HCMS06112	HCMA06112	HPMS06112	HPMA06112	HJMS06112
			HCMS061**	HCMA061**	HPMS061**	HPMA061**	HJMS061**

Note: ▲ Replace ** with length required in feet. For nylon coupling nuts, replace "M" with "N" per the ordering chart above.
Example: change **HPMA05106** to **HPNA05106**.