

Choose the appropriate configuration from the Selector below.

### Hubbell Logic Configurator

For example, catalog number **HCMA08112** is derived as follows:

DEVICE TYPE	COUPLING NUT MATERIAL	BODY STYLE	POLES	CONDUCTOR TYPE	CABLE LENGTH (ft)
<b>HC</b> = Plug, Female <b>HP</b> = Plug, Male <b>HJ</b> = Male/Female Jumper Cable	<b>M</b> = Metallic <b>N</b> = Nylon	<b>A</b> = Right Angle <b>S</b> = Straight	07 08 09 10 12	1 = #16 AWG SEOOW Cable	** 03 06 12 20  **Replace with Length
<b>HC</b>	<b>M</b>	<b>A</b>	<b>08</b>	<b>1</b>	<b>12</b>

Note: Availability of specific items may vary. Consult factory for delivery. Consult the factory for additional cable lengths or cable types.

### 7 - 12 Pole Plugs

Catalog numbers using #16 AWG SEOOW cable are listed below.

Poles	Male Face Shown Female - mirror image	Cable Length	Female Plugs		Male Plugs		Male/Female JumperCables
			Straight	Right Angle	Straight	Right Angle	Straight
7		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	<b>HCMS07103</b>	<b>HCMA07103</b>	<b>HPMS07103</b>	<b>HPMA07103</b>	<b>HJMS07103</b>
			<b>HCMS07106</b>	<b>HCMA07106</b>	<b>HPMS07106</b>	<b>HPMA07106</b>	<b>HJMS07106</b>
			<b>HCMS07112</b>	<b>HCMA07112</b>	<b>HPMS07112</b>	<b>HPMA07112</b>	<b>HJMS07112</b>
			<b>HCMS071**</b>	<b>HCMA071**</b>	<b>HPMS071**</b>	<b>HPMA071**</b>	<b>HJMS071**</b>
8		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	<b>HCMS08103</b>	<b>HCMA08103</b>	<b>HPMS08103</b>	<b>HPMA08103</b>	<b>HJMS08103</b>
			<b>HCMS08106</b>	<b>HCMA08106</b>	<b>HPMS08106</b>	<b>HPMA08106</b>	<b>HJMS08106</b>
			<b>HCMS08112</b>	<b>HCMA08112</b>	<b>HPMS08112</b>	<b>HPMA08112</b>	<b>HJMS08112</b>
			<b>HCMS081**</b>	<b>HCMA081**</b>	<b>HPMS081**</b>	<b>HPMA081**</b>	<b>HJMS081**</b>
9		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	<b>HCMS09103</b>	<b>HCMA09103</b>	<b>HPMS09103</b>	<b>HPMA09103</b>	<b>HJMS09103</b>
			<b>HCMS09106</b>	<b>HCMA09106</b>	<b>HPMS09106</b>	<b>HPMA09106</b>	<b>HJMS09106</b>
			<b>HCMS09112</b>	<b>HCMA09112</b>	<b>HPMS09112</b>	<b>HPMA09112</b>	<b>HJMS09112</b>
			<b>HCMS091**</b>	<b>HCMA091**</b>	<b>HPMS091**</b>	<b>HPMA091**</b>	<b>HJMS091**</b>
10		3 ft (0.91m) 6 ft (1.83m) 12 ft (3.66m) All other lengths▲	<b>HCMS10103</b>	<b>HCMA10103</b>	<b>HPMS10103</b>	<b>HPMA10103</b>	<b>HJMS10103</b>
			<b>HCMS10106</b>	<b>HCMA10106</b>	<b>HPMS10106</b>	<b>HPMA10106</b>	<b>HJMS10106</b>
			<b>HCMS10112</b>	<b>HCMA10112</b>	<b>HPMS10112</b>	<b>HPMA10112</b>	<b>HJMS10112</b>
			<b>HCMS101**</b>	<b>HCMA101**</b>	<b>HPMS101**</b>	<b>HPMA101**</b>	<b>HJMS101**</b>
12		3 ft/0.91m) 6 ft/1.83m) 12 ft/3.66m) All other lengths▲	<b>HCMS12103</b>	<b>HCMA12103</b>	<b>HPMS12103</b>	<b>HPMA12103</b>	<b>HJMS12103</b>
			<b>HCMS12106</b>	<b>HCMA12106</b>	<b>HPMS12106</b>	<b>HPMA12106</b>	<b>HJMS12106</b>
			<b>HCMS12112</b>	<b>HCMA12112</b>	<b>HPMS12112</b>	<b>HPMA12112</b>	<b>HJMS12112</b>
			<b>HCMS121**</b>	<b>HCMA121**</b>	<b>HPMS121**</b>	<b>HPMA121**</b>	<b>HJMS121**</b>

Note: ▲ Replace \*\* with length required in feet. For nylon coupling nuts, replace "M" with "N" per the ordering chart above.  
Example: change **HPMA07106** to **HPNA07106**.