



**GFR5362SGI**

**10kA Short Circuit Current Rating**

- Limits improper access to energized contacts
  - Exclusive patented tamper-resistant protection through switching technology
- Continually tests and monitors for people protection automatically
  - Patented self test diagnostics
- Power indication
  - Steady **"ON" GREEN LED** provides indication of power
- Ground fault indicator
  - Steady **"ON" RED LED** provides visual indication of a ground fault condition; flashing red indicates device has lost capability to provide protection
- No power at face if reverse wired
  - Open circuit condition eliminates false assumption of protection at face
- Durable face with V-0 flammability rating
  - Polyester face cover


**AUTOGUARD® Self Test GFCI Receptacles**  
**Tamper-Resistant and Weather Resistant**



**GFR5262SG**

Description	Rating	Color	Catalog Number	
Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	<b>GFR5262SGBK</b>	<b>GFR5362SGBK</b>
		Brown	<b>GFR5262SG</b>	<b>GFR5362SG</b>
		Gray	<b>GFR5262SGGY</b>	<b>GFR5362SGGY</b>
		Ivory	<b>GFR5262SGI</b>	<b>GFR5362SGI</b>
		Red	<b>GFR5262SGR</b>	<b>GFR5362SGR</b>
		White	<b>GFR5262SGW</b>	<b>GFR5362SGW</b>
Hospital Grade  Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	<b>GFR8200SGBK</b>	<b>GFR8300SGBK</b>
		Brown	<b>GFR8200SG</b>	<b>GFR8300SG</b>
		Gray	<b>GFR8200SGGY</b>	<b>GFR8300SGGY</b>
		Ivory	<b>GFR8200SGI</b>	<b>GFR8300SGI</b>
		Red	<b>GFR8200SGR</b>	<b>GFR8300SGR</b>
		White	<b>GFR8200SGW</b>	<b>GFR8300SGW</b>

**Circuit Guard® GFCI Receptacles**  
**Tamper-Resistant and Weather Resistant**



**GFR5262GYTR**

Description	Rating	Color	Catalog Number	
Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	<b>GFR5262BKTR</b>	<b>GFR5362BKTR</b>
		Brown	<b>GFR5262TR</b>	<b>GFR5362TR</b>
		Gray	<b>GFR5262GYTR</b>	<b>GFR5362GYTR</b>
		Ivory	<b>GFR5262ITR</b>	<b>GFR5362ITR</b>
		Red	<b>GFR5262RTR</b>	<b>GFR5362RTR</b>
		White	<b>GFR5262WTR</b>	<b>GFR5362WTR</b>
Hospital Grade  Flush, polyester face, back and side wired, multiple drive screws.	15 and 20A 125V AC	Black	<b>GFR8200BKTR</b>	<b>GFR8300BKTR</b>
		Brown	<b>GFR8200TR</b>	<b>GFR8300TR</b>
		Gray	<b>GFR8200GYTR</b>	<b>GFR8300GYTR</b>
		Ivory	<b>GFR8200ITR</b>	<b>GFR8300ITR</b>
		Red	<b>GFR8200RTR</b>	<b>GFR8300RTR</b>
		White	<b>GFR8200WTR</b>	<b>GFR8300WTR</b>

*Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with both a matching color nylon wallplate, and a SS26 302/304 super stainless steel wallplate. 20 amp feed-through capability. See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.*