




**HBL25515**

**IP30**  
 SUITABILITY



**50A 250V AC**



**60A 250V AC**


**Mobile X-Ray Plugs**

Description	Catalog Number	
Plug, with epoxy kit, less cord clamp.	<b>HBL25515</b>	<b>HBL25615</b>
Plug, with cord clamp, less epoxy kit.	<b>HBL25525</b>	<b>HBL25625</b>


*Note: Cord clamp range of plugs with cord clamps .830" to 1.3" (21.1 to 33.0).  
 50A plugs fit 50A or 60A receptacles.*



**HBL25615**




**50A 250V AC**



**60A 250V AC**

**Mobile X-Ray Receptacles**


Description	Catalog Number	
Receptacle with stainless steel plate assembly.	<b>HBL25505</b>	<b>HBL25605</b>
Receptacle with cast aluminum plate assembly.	<b>HBL25503</b>	<b>HBL25603</b>
Replacement receptacle interior.	-	<b>IN16494</b>




**HBL25605**

**Accessory**

Description	Catalog Number
Box stamped steel 8" x 8" x 4" (203.2 x 203.2 x 101.6), accommodates 50A and 60A mobile X-ray receptacles. Knockout sizes 1¼", 1½" and 2".	<b>HBL25509</b>



**HBL25603**



**HBL25509**

Dimensions in Inches (mm)