








Telephone and Coaxial Outlet Plates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 <p>1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount</p>	Almond	NP11AL	NPJ11AL	Aluminum	①
	Black	NP11BK	-	Brass	①
	Brown	NP11	NPJ11	Brass Plated	①
	Gray	NP11GY	-	Chrome	①
	Ivory	NP11I	NPJ11I	S/S 302/304	SS11*
	Light Almond	NP11LA	NPJ11LA	S/S 430	SS11L*
	Red	NP11R	-		
	White	NP11W	NPJ11W		
 <p>1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Strap Mount</p>	Almond	NP12AL	-	Aluminum	①
	Black	NP12BK	-	Brass	SB12*
	Brown	NP12	-	Brass Plated	SBP12*
	Gray	NP12GY	-	Chrome	SCH12*
	Ivory	NP12I	-	S/S 302/304	SS12*
	White	NP12W	-	S/S 430	SS12L*
 <p>1-Gang, 1-Tel .625 in. (15.9) Hole, Box Mount</p>	Almond	NP737AL	-	Aluminum	-
	Brown	NP737	-	Brass	-
	Ivory	NP737I	-	Brass Plated	-
	White	NP737W	-	Chrome	-
				S/S 302/304	-
 <p>1-Gang, 1-Tel .625 in. (15.9) Hole, Strap Mount</p>	Brown	NP730	-	Aluminum	-
	Ivory	NP730I	-	Brass	-
	White	NP730W	-	Brass Plated	-
				Chrome	-
				S/S 302/304	-
 <p>1-Gang, 1-Tel .380 in. (9.7) Hole, Box Mount or Strap Mount</p>	Almond	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Ivory	-	-	Brass Plated	①
	White	-	-	Chrome	①
				S/S 302/304	SS739
				S/S 302/304, Strap Mount	SS738
 <p>2-Gang, 2-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount</p>	Black	NP21BK	-	Aluminum	①
	Brown	NP21	-	Brass	①
	Gray	NP21GY	-	Brass Plated	①
	Ivory	NP21I	-	Chrome	①
	White	NP21W	-	S/S 302/304, Strap Mount	SS22*
				S/S 430	-
 <p>2-Gang, 1-Tel .640 in. (16.3) Hole, Box Mount</p>	Almond	-	-	Aluminum	-
	Brown	-	-	Brass	-
	Ivory	-	-	Brass Plated	-
	White	-	-	Chrome	-
				S/S 302/304	SS741*
			S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.
 ① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.
 *.50" (12.7) I.D. nylon bushing provided.