

IP66
 SUITABILITY



RW57300

1-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 3.5" x 2.8" (147.3 x 88.9 x 71.1)		RW57300



RW57350

Thermoplastic, gray, extra deep, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 3.5" x 4.8" (147.3 x 88.9 x 121.9)	RW57350
--	--	----------------



1-Gang Weatherproof Covers for Horizontal Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	4.0" x 5.2" x 2.8" (101.6 x 132.1 x 71.1)		RW57400



RW57400



RW57750

2-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 2.8" (147.3 x 134.6 x 71.1)		RW57750



RW57900

Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 4.8" (147.3 x 134.6 x 121.9)	RW57900
--	---	----------------



RW57950

Thermoplastic, gray, single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 4.8" (147.3 x 134.6 x 121.9)	RW57950
---	---	----------------



Note: Required by the NEC® for while-in-use outdoor power distribution. Thermoplastic covers provide protection for use in wet locations with the cover closed, NEMA® 3R rated. Meets NEC 406.8 – receptacles in damp or wet locations. Holes for padlocks are .40 inch.

*NEC® is a registered trademark of the The National Electrical Code.
 NEMA® is a registered trademark of The National Electrical Manufacturers Association.*