

Fire-Rated Poke-Throughs for Concrete Floors Hubbell SystemOne Recessed Systems 6 Inch Sub-Plates

60/40 Device Plate Combination

- Allows for up to twelve data/AV jacks plus a 20A duplex receptacle
- Two plates which can be wired independently







50/50 Device Plate Combination



- Allows for up to eight Hubbell data jacks plus two 20A duplex receptacles
- Two plates which can be wired independently



Left 60% Sub-Plates

Description	Catalog Number	Description	Catalog Number
(1) Style Line® Decorator and (2) Extron® MAAP openings, left side only	 S1R6SPV	(1) Style Line® Decorator and (2) Extron® AAP openings, left side only	 S1R6SPX
(2) Style Line® Decorator openings, left side only	 S1R6SPW	(1) Style Line® Decorator and (2) 1.5 unit Hubbell iSTATION openings, left side only (See section W for modules)	 S1R6SPY

Right 40% Sub-Plates

(2) 20A pre-wired receptacles; 16 inch lead; one circuit, right side only (Supplied with isolated ground sticker)	 S1R6SPZ	(2) 20A pre-wired receptacles; 25 foot lead; one circuit, right side only (Supplied with isolated ground sticker)	 S1R6SPZ25
---	--	---	--

Recessed 6 Inch Cover

6 Inch Fire-Rated Poke-Through cover assembled unit includes solid cast aluminum construction, carpet gasket and mounting hardware.











Finish	Catalog Number	Furniture Feed Option
Brushed Aluminum	S1R6CVRALU	S1R6FFCVRALU
Black Powder Coat	S1R6CVRBLK	S1R6FFCVRBLK
Brushed Brass Plated	S1R6CVRBRS	S1R6FFCVRBRS
Bronze Plated Finish	S1R6CVRBRZ	S1R6FFCVRBRZ
Satin Nickel Plated	S1R6CVRNKL	S1R6FFCVRNKL

6 Inch Accessories






Description	Catalog Number
Pre-pour tube, including hardware	S1R6PPT*
Abandonment plate, black finish	S1R6ADMTBK
Low voltage replacement divider	S1R6DIV
Power junction box, 27.0 cubic inches; (1) 3/4 inch and (1) 1 inch EMT connector	S1FRPTJB
Replacement furniture feed fitting	2 Inch S1RFFFIT2 3/4 Inch S1RFFFIT075
Replacement plugs	2 Inch S1RPLUG2ALU 3/4 Inch S1RPLUG075ALU Aluminum S1RPLUG2BLK S1RPLUG075BLK Black S1RPLUG2BRS S1RPLUG075BRS Brass S1RPLUG2BRZ S1RPLUG075BRZ Bronze S1RPLUG2NKL S1RPLUG075NKL Nickel

Note: *Not UL Listed.

Left 50% Sub-Plates

Description	Catalog Number	Description	Catalog Number
(3) Extron® AAP plate openings, left side only	 S1R6SPA	Blank cover plate, left side only	 S1R6SPB
(5) Extron® MAAP plate openings, left side only	 S1R6SPC	(4) 1 unit Hubbell iSTATION openings, left side only (See section W for modules)	 S1R6SPD
(1) Style Line® Decorator and (2) Hubbell keystone openings, left side only	 S1R6SPE	(2) 1.5 unit Hubbell iSTATION openings, left side only (See section W for modules)	 S1R6SPF
(3) Extron® MAAP openings and (2) Hubbell keystone jack openings, left side only	 S1R6SPL	(1) Style Line® Decorator opening, left side only	 S1R6SPM

Right 50% Sub-Plates

(1) 1.60 inch opening for 20A and 30A Twist-Lock®, right side only	 S1R6SPG	(4) 20A pre-wired receptacles; 16 Inch leads; one or two circuits, right side only (Supplied with isolated ground sticker)	 S1R6SPH
(1) Duplex device opening, right side only	 S1R6SPI	(1) 1.40 inch opening for simplex or 15A Twist-Lock®, right side only	 S1R6SPJ
(1) Style Line® Decorator device opening, right side only	 S1R6SPK		

Note: Sub-plates can not be rotated to create additional layouts. When assembled, sub-plates can not overlap.
Custom Plates available upon request and may be subject to minimum order quantity.

Extron® is a registered trademark of Extron Electronics.