



Features

- Material: 16 gauge tubular steel
- Durable powder coat
- Stringer dimensions: 0.375" W x 1.5" H
- Rung spacing: 9.0"
- Weight capacity: 45lb/foot



Straight Section
HLS0612G



Flat Turn 90°
HLF1290G



Inside Radius 90°
HLI1290G

Straight Sections

Width Inches (mm)	6' (1829) Length	
	Black	Gray
6" (152)	HLS0606B	HLS0606G
12" (305)	HLS0612B	HLS0612G
18" (457)	HLS0618B	HLS0618G
24" (610)	HLS0624B	HLS0624G

Width Inches (mm)	10' (3048) Length	
	Black	Gray
6" (152)	HLS1006B	HLS1006G
12" (305)	HLS1012B	HLS1012G
18" (457)	HLS1018B	HLS1018G
24" (610)	HLS1024B	HLS1024G

Note: Width = outside to outside dimensions.

90° Turns

Width Inches (mm)	Inside Radius 90°	
	Black	Gray
6" (152)	HLI0690B	HLI0690G
12" (305)	HLI1290B	HLI1290G
18" (457)	HLI1890B	HLI1890G
24" (610)	HLI2490B	HLI2490G

Width Inches (mm)	Outside Radius 90°	
	Black	Gray
6" (152)	HLO0690B	HLO0690G
12" (305)	HLO1290B	HLO1290G
18" (457)	HLO1890B	HLO1890G
24" (610)	HLO2490B	HLO2490G

Width Inches (mm)	Flat Turns 90°	
	Black	Gray
6" (152)	HLF0690B	HLF0690G
12" (305)	HLF1290B	HLF1290G
18" (457)	HLF1890B	HLF1890G
24" (610)	HLF2490B	HLF2490G